



TOOLCRAFT

DATASHEET

Solder Fume Extractor

Item No. 1553619

Delivery

- Product
- Activated carbon filter
- Operating instructions



Technical data

Product

Input	220 - 240 V/AC 50 Hz
Power	23 W
Airflow	10 m³/h, 72 m³/h
Noise level	45 dB
Operating conditions	-6 to +46 °C, 10 - 90 % RH
Storage conditions	-20 to +60 °C, 10 - 70 %
Cable length	1.4 m
Dimensions (W x H x D)	135 x 217 x 185 mm
Weight	1042 g

Filter

Filter type	Activated carbon
Carbon content	35 - 65 %
Benzene absorption rate	25 - 32 %
Resistance	1 m/s
Dimensions (W x H x D)	130 x 130 x 10 mm

