

- High power density in low profile case, module depth < 55 mm
- Suitable for mounting in domestic installation panels
- Very high efficiency and low standby power -> compliance to ECO-Standard
- Low output ripples and spikes
- Suitable for household appliance and industrial application
- For distributed power
- Operating temperature range: -25°C to +70°C
- UL 508 listed
- 3-year product warranty



This new DIN-Rail mounting power supplies are designed for industrial and residential applications. They are lower cost than the existing TBL range, with similar electrical specifications. Additionally, they fully comply to the new standby power and efficiency requirements (ECO Standard). They are intended for connecting as class II devices, so the safety earth connection is not required. They are mountable in flat racks due to their small dimensions in depth. Their dimensions comply to the DIN 43880 standard.

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TBLC 90-112	90 W	12 VDC (12.0 - 16.0 VDC)	7'500 mA	90 %
TBLC 90-124		24 VDC (24.0 - 28.0 VDC)	3'750 mA	90 %

Input Specifications

Input Voltage		Operational Range: 85 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
Input Frequency		Operational Range: 47 - 63 Hz Certified: 50/60 Hz
Power Consumption	- No load & $V_{in} = 230$ VAC - No load & $V_{in} = 115$ VAC	500 mW max. (Ready to meet ErP directive) 500 mW max.
Input Inrush Current	- At 230 VAC - At 115 VAC	50 A max. 25 A max.
Recommended Input Fuse		(The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		12 VDC model: 12.0 - 16.0 VDC 24 VDC model: 24.0 - 28.0 VDC (By trim potentiometer) Output power must not exceed rated power!
Voltage Set Accuracy		±0.5% max.
Regulation	- Input Variation ($V_{min} - V_{max}$) - Load Variation (10 - 90%)	0.3% max. 0.3% max.
Ripple and Noise (20 MHz Bandwidth)		50 mVp-p max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Hold-up Time	- At 230 VAC - At 115 VAC	60 ms min. 15 ms min.
Start-up Time	- At 230 VAC - At 115 VAC	1'000 ms max. 1'000 ms max.
Short Circuit Protection		Continuous, Automatic recovery 70 - 90% of $I_{out\ nom.}$ (12 Vout model) 120 - 200% of $I_{out\ nom.}$ (24 Vout model)
Overload Protection		Constant Current Mode
Output Current Limitation		105 - 130% of $I_{out\ max.}$
Overvoltage Protection		125 - 150% of $V_{out\ nom.}$
Transient Response	- Peak Variation - Response Time	400 mV max. (10% to 90% Load Step) 1'000 μs typ. (10% to 90% Load Step)

Safety Specifications

Safety Standards	- IT / Multimedia Equipment - Industrial Control Equipment - Household - Machines Equipment - Power Installation - Measurement, Control & Lab. - Power Transformers - Converter System - Certification Documents	EN 60950-1 IEC 60950-1 UL 60950-1 UL 508 EN 60335-1 IEC 60335-1 EN 60204 EN 50178 EN 61010-1 EN 61010-2-201 IEC 61010-1 IEC 61010-2-201 EN 61558-2-8 EN 61558-2-16 EN 62477 IEC 62477 www.tracopower.com/overview/tb1c90
------------------	--	--

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Protection Class	Class I & II (Prepared): Reinforced Insulation
Class 2 Power Units	UL 1310 (24 Vout model only)
Pollution Degree	PD 2
Over Voltage Category	OVC II

EMC Specifications

EMI Emissions		EN 61000-6-3 (Generic Residential) EN 61204-3 (Low Voltage Power Supplies) EN 55011 class B (internal filter) EN 55014-1 (internal filter) EN 55032 class B (internal filter)
- Conducted Emissions		EN 55011 class B (internal filter) EN 55014-1 (internal filter) EN 55032 class B (internal filter)
- Radiated Emissions		EN 55011 class B (internal filter) EN 55014-1 (internal filter) EN 55032 class B (internal filter)
- Harmonic Current Emissions		EN 61000-3-2, class A
EMS Immunity		EN 61000-6-2 (Generic Industrial) EN 61204-3 (Low Voltage Power Supplies)
- Electrostatic Discharge	Air:	EN 61000-4-2, ±8 kV, perf. criteria B
	Contact:	EN 61000-4-2, ±4 kV, perf. criteria B
- RF Electromagnetic Field		EN 61000-4-3, 10 V/m, perf. criteria A
- EFT (Burst) / Surge		EN 61000-4-4, ±2 kV, perf. criteria B
	L to L:	EN 61000-4-5, ±1 kV, perf. criteria B
	L to PE:	EN 61000-4-5, ±2 kV, perf. criteria B
- Conducted RF Disturbances		EN 61000-4-6, 10 Vrms, perf. criteria A
- PF Magnetic Field	Continuous:	EN 61000-4-8, 30 A/m, perf. criteria A
- Voltage Dips & Interruptions	230 VAC / 50 Hz:	EN 61000-4-11 30%, 25 periods, perf. criteria A 60%, 10 periods, perf. criteria B >95%, 1 period, perf. criteria A
	115 VAC / 60 Hz:	EN 61000-4-11 30%, 25 periods, perf. criteria B 60%, 10 periods, perf. criteria B >95%, 1 period, perf. criteria B
- Voltage Sag Immunity		SEMI F47, criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-25°C to +70°C
	- Case Temperature	+70°C max.
	- Storage Temperature	-40°C to +85°C
Power Derating	- High Temperature	2.5 %/K above 55°C
	- Low Input Voltage	2 %/V below 100 VAC
Cooling System		Natural convection (20 LFM)
Altitude During Operation		5'000 m max. (Lower altitude required for IEC61558-1 & 60335 of 3000 m)
Switching Frequency		60 - 87 kHz (PWM)
Insulation System		Reinforced Insulation
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC
Creepage	- Input to Output	4.5 mm min.
Clearance	- Input to Output	3.7 mm min.
Leakage Current	- Touch Current	250 µA max.
Reliability	- Calculated MTBF	1'900'000 h (IEC 61709)
Environment	- Vibration	IEC 60068-2-6 2 g, 3 axis, sine sweep, 3x60 min, 10-150 Hz
	- Mechanical Shock	IEC 60068-2-27 30 g, 3 axis, half sine, 11 ms

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.


Case Ingress Protection	IP 20 (acc. IEC 60529)
Housing Material	Plastic (UL 94 V-2 rated)
Housing Type	Plastic Case
Mounting Type	DIN-Rail Mount (EN 60715 - 35x7.5mm/35x15mm)
Connection Type	Screw Terminal
Weight	280 g
Thermal Impedance - Case to Ambient	1.8 K/W typ.
Status Indicator	Indicated by green LED
Environmental Compliance - REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant
- RoHS Declaration	www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule))
- SCIP Reference Number	a7f5b9e9-3ce9-4da8-88e0-fa965c7848b9

Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tbhc90

Outline Dimensions



Wiring		
Description	Wire size	Torque
AC Input all models: L, N only (2 pin terminal)	AWG 20 - 14 0.5 - 2.5 mm ² max.	0.5 Nm
DC Output double terminal	AWG 20 - 14 0.5 - 2.5 mm ² max.	0.5 Nm