

Safety relays - PSR-MC60-2NO-1DO-24DC-SC - 2700571

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Safety relay for two-hand control devices according to EN 574 type IIIA, up to SILCL 1, Cat. 1, PL c, synchronous activation monitoring < 0.5 s, 2 enabling current paths, $U_S = 24\text{ V DC}$, plug-in screw terminal block

Your advantages

- Up to Cat. 1/PL c according to ISO 13849-1, SILCL 1 according to IEC 62061
- Type IIIA according to EN 574
- Low housing width of just 12.5 mm
- 2 enabling current paths, 1 digital signal output
- Automatic activation



Key commercial data

package_quantity	1
GTIN	4046356988353

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
--------------------------------	---

Dimensions

Width	12.5 mm
Height	112.2 mm
Depth	114.5 mm

Ambient conditions

Ambient temperature (operation)	-35 °C ... 60 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g
Vibration (operation)	10 Hz ... 150 Hz, 2g
Maximum altitude	≤ 2000 m (Above sea level)

Input data

Safety relays - PSR-MC60-2NO-1DO-24DC-SC - 2700571

Technical data

Input data

Rated control circuit supply voltage U_s	24 V DC -20 % / +25 %
Rated control supply current I_s	typ. 35 mA
Power consumption at U_s	typ. 0.9 W
Inrush current	typ. 20 A ($\Delta t = 10 \mu s$ at U_s)
Current consumption	< 5.1 mA (with U_s/I_x at S12/S35)
Current consumption	> -5.1 mA (with U_s/I_x to S22)
Voltage at input/start and feedback circuit	24 V DC -20 % / +25 %
Typical response time	< 40 ms
Typical release time	< 10 ms (when controlled via S12/S22)
Typical release time	< 5 ms (when interrupted via A1; applicative deactivation via A1/A2 is not permitted)
Concurrence input 1/2	< 0.5 s
Recovery time	< 500 ms
Status display	2 x green LEDs
Maximum switching frequency	1 Hz
Max. permissible overall conductor resistance	150 Ω
Filter time	10 ms (For the logic. At A1 in the event of voltage dips at U_s)

Output data

Contact type	2 enabling current paths
Contact material	AgSnO ₂
Minimum switching voltage	12 V AC/DC
Maximum switching voltage	250 V AC/DC (Observe the load curve)
Limiting continuous current	6 A (observe derating)
Inrush current, minimum	3 mA
Maximum inrush current	6 A
Sq. Total current	72 A ² (observe derating)
Switching capacity	min. 60 mW
Output fuse	6 A gL/gG (N/O contact)

Alarm outputs

Number of outputs	1 (digital, PNP)
Voltage	22 V DC ($U_s - 2 V$)
Current	max. 100 mA
Maximum inrush current	500 mA ($\Delta t = 1 ms$ at U_s)
Short-circuit protection	Yes

General

Relay type	Electromechanical relay with forcibly guided contacts in accordance with IEC/EN 61810-3 (EN 50205)
Mechanical service life	10 x 10 ⁶ cycles
Nominal operating mode	100% operating factor
Net weight	147.3 g

Safety relays - PSR-MC60-2NO-1DO-24DC-SC - 2700571

Technical data

General

Mounting type	DIN rail mounting
Assembly instructions	See derating curve
Mounting position	vertical or horizontal
Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Housing material	PBT
Housing color	yellow

Connection data

Connection method	Screw connection
pluggable	Yes
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	7 mm
Screw thread	M3

Safety-related characteristic data

Stop category	0
Designation	IEC 61508 - High demand
Safety Integrity Level (SIL)	1 (4 A DC13; 5 A AC15; 8760 switching cycles/year)
Designation	EN ISO 13849
Performance level (PL)	c (4 A DC13; 5 A AC15; 8760 switching cycles/year)
Category	1 (4 A DC13; 5 A AC15; 8760 switching cycles/year)
Designation	EN 62061
Safety Integrity Level Claim Limit (SIL CL)	1 (4 A DC13; 5 A AC15; 8760 switching cycles/year)

Standards and Regulations

Shock	15g
Designation	Air clearances and creepage distances between the power circuits
Standards/regulations	DIN EN 50178
Rated insulation voltage	250 V AC
Rated insulation voltage	250 V AC
Rated surge voltage/insulation	Basic insulation 4 kV between all current paths and housing
Rated surge voltage/insulation	Safe isolation, reinforced insulation 6 kV:between (A1, A2, S11, S12, S21, S22, S35, M1) and enabling current path (13/14)between (A1, A2, S11, S12, S21, S22, S35, M1) and enabling current path (23/24)between enabling current paths
Degree of pollution	2
Overvoltage category	III
Vibration (operation)	10 Hz ...150 Hz, 2g

Safety relays - PSR-MC60-2NO-1DO-24DC-SC - 2700571

Technical data

Standards and Regulations

Conformance	CE-compliant
--------------------	--------------

Classifications

eCl@ss

eCl@ss 5.1	27371901
eCl@ss 6.0	27371819
eCl@ss 8.0	27371819
eCl@ss 9.0	27371819

ETIM

ETIM 5.0	EC001449
-----------------	----------

UNSPSC

UNSPSC 13.2	39121501
--------------------	----------

Approvals

UL Listed / cUL Listed / Functional Safety / cULus Listed /

Approval details

UL Listed


cUL Listed

Functional Safety

cULus Listed


Drawings

Block diagram



Safety relays - PSR-MC60-2NO-1DO-24DC-SC - 2700571

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>