



LITHIUM BUTTON CELL

Document Title: Pb041632

CR 1632




Chemical System : Lithium/Manganese Dioxide
 IEC Name: CR1632
 Camelion Model: CR1632
 Average Weight : 2.0g
 Dimension (Ø x H) : $16.0^{-0.3} \times 3.2^{-0.3}$ mm
 $0.63^{-0.01} \times 0.13^{-0.01}$ inch




Unit: mm(inch)

Terminals: Flat
 Nominal Voltage : 3.0Volts
 Capacity : 120mAh
 (20±2°C, under 15kΩ load to 2.00V)
 Standard Discharge Current: 0.1mA
 Max. Continuous Discharge Current: 0.3mA
 Max. Pulse Discharge Current: 2.5mA
 Operating Temperature: -20°C- 60°C
 Storage Conditions
 Temperature: 0°C-30°C
 Relative Humidity: 60±15%
 Cross Reference: E-CR1632(Energizer),
 DL1632(Duracell), KECR1632(Rayovac)

Discharge characteristics



Temperature Characteristics



Notice:

Environmental elements comply with RoHS requirements. This information is subject to change without prior notice and for reference only. It should not be used as a basis for a product guarantee or warranty. For additional information, please consult your nearest Camelion Sales Office or Distributor or visit our website at: www.camelionbattery.com.