


#### Measurement:



#### Technical characteristics:

## Protection index:

- IP 66 and IP69K following IEC 60529
- NEMA 4x,12,13
- IP 20 at the back of panel following IEC 60529

### Protection against mechanical impact:

IK 05 following IEC 62262

#### Operating voltage:

- 24 V AC/DC (+/- 10%)
- 130 V AC/DC\* (+/- 10%)
- 230 V AC/DC\* (+/- 10%)
  \*Declarative rating

# Terminals:

Screw terminals

#### Tightening torque for terminals:

• Recommended 1.2N.m.

#### Consumption:

24V: 4.6mA130V: 5.2mA230V: 4.6mA

#### Lifetime at rated supply voltage:

Red: 100 000 hours at 25°C

Others colours: 50 000 hours at 25°C

#### Insulation voltage:

• 300 V

#### Pollution degree:

• 3

## Tightening torque for locking ring:

 Recommended 3 N.m. or tightened with fixing tool to hand tight after pressure point plus another half turn

#### Electrical insulation:

Classe II according to IEC 60947-5-1

# Operating temperature :

• . minimum : -25°C maximum : +70°C

# Storage Temperature :

• . minimum : -40°C maximum : +70°C

## Cold test:

according to IEC 60068-2-1

#### Dry heat test:

• . according to IEC 60068-2-2

#### Constant humidity test:

according to IEC 60068-2-3

#### Materials:

PC (Lens)

#### Certifications and conformity:

- CB test (IEC 60947-5-1); CE; CCC; UL and BV
- Compliant with RoHs and Reach

# Packaging:

• Minimum Order Quantity=10

#### Guarantee:

• 10 years guarantee

