

Mini ground terminal block - MUT 4-PE - 3248037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Mini ground terminal block, Connection method: Screw connection, Number of connections: 2, Cross section: 0.2 mm² - 6 mm², AWG: 24 - 10, Width: 6.2 mm, Color: green-yellow, Mounting type: NS 15

Your advantages

- ✓ Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- ✓ Clear arrangement thanks to marking of all terminal points
- ✓ Easy potential distribution thanks to standardized plug-in bridges



Key commercial data

package_quantity	50
GTIN	4046356801515

Technical data

General

Number of levels	1
Number of connections	2
Potentials	1
Nominal cross section	4 mm ²
Color	green-yellow
Insulating material	PA
Flammability rating according to UL 94	V0

General

Rated surge voltage	6 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Open side panel	Yes
Oscillation, broadband noise test result	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 2, bogie-mounted
Test frequency	f ₁ = 5 Hz to f ₂ = 250 Hz

Mini ground terminal block - MUT 4-PE - 3248037

Technical data

General

ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12 g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Shock test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	5 g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	6.2 mm
End cover width	2.2 mm
Length	29.9 mm
Height NS 15	34 mm

Connection data

Note	Please observe the current carrying capacity of the DIN rails.
Connection method	Screw connection
Connection in acc. with standard	IEC 60947-7-2
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section AWG min.	24

Mini ground terminal block - MUT 4-PE - 3248037

Technical data

Connection data

Conductor cross section AWG max.	10
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	6 mm ²
Min. AWG conductor cross section, flexible	24
Max. AWG conductor cross section, flexible	10
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	4 mm ²
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

Standards and Regulations

Connection in acc. with standard	CSA
Connection in acc. with standard	IEC 60947-7-2
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141141
eCl@ss 9.0	27141141

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000901
ETIM 5.0	EC000901

Mini ground terminal block - MUT 4-PE - 3248037

Classifications

ETIM

ETIM 6.0	EC000901
-----------------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

IECEEx / ATEX / EAC Ex / CSA / UL Recognized / cUL Recognized / VDE Zeichengenehmigung / IECEx CB Scheme / GL / BV / DNV / EAC / EAC / cULus Recognized /

Approval details

IECEEx	
Nominal voltage UN	
Nominal current IN	
mm ² /AWG/kcmil	0.2-6

ATEX 	
Nominal voltage UN	
Nominal current IN	
mm ² /AWG/kcmil	0.2-6

EAC Ex

CSA 	
Nominal voltage UN	
Nominal current IN	
mm ² /AWG/kcmil	20-10

UL Recognized 		
Usegroups	B	C
Nominal voltage UN		
Nominal current IN		
mm ² /AWG/kcmil	24-10	24-10

Mini ground terminal block - MUT 4-PE - 3248037

Approvals

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN		
Nominal current IN		
mm²/AWG/kcmil	24-10	24-10

VDE Zeichengenehmigung 	
Nominal voltage UN	500 V
Nominal current IN	
mm²/AWG/kcmil	0.2-2.5

IECEE CB Scheme 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.2-2.5

GL 
--

BV 
--

DNV 

EAC 

EAC

cULus Recognized 
--

Accessories

End cover

D-MUT 2,5/4 - 3248033



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

Screwdriver tools

SZS 0,6X3,5 - 1205053



Jumper

FBS 2-6 - 3030336



FBS 3-6 - 3030242



FBS 4-6 - 3030255



FBS 5-6 - 3030349



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

FBS 6-6 - 1008238



FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



FBSR 2-6 - 3033715



FBSR 3-6 - 3001594



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

FBSR 4-6 - 3001595



FBSR 5-6 - 3001596



FBSR 10-6 - 3033716



Short-circuit connector

FBSRH 2-6 - 3033812



DIN rail

NS 15 UNPERF 2000MM - 1401695



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

NS 15 PERF 2000MM - 1401682

NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



End block

CLIPFIX 15 - 3022263



Terminal marking

ZBF 6:UNBEDRUCKT - 0808710



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

UC-TMF 6 - 0818140



UCT-TMF 6 - 0828746



Labeled terminal marker

ZBF 6 CUS - 0825027



UC-TMF 6 CUS - 0824646



UCT-TMF 6 CUS - 0829665



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

ZBF 6,LGS:FORTL.ZAHLEN - 0808749



ZBF 6,QR:FORTL.ZAHLEN - 0808765



ZBF 6,LGS:GERADE ZAHLEN - 0810834



ZBF 6,LGS:UNGERADE ZAHLEN - 0810876



Test plug terminal block

MPS-MT - 0201744



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

PS-6 - 3030996



PS-6/2,3MM RD - 3038736



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

CLIP-PROJECT PROFESSIONAL - 5146053



Test socket

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PAI-4-FIX-5/6 WH - 3035983



Mini ground terminal block - MUT 4-PE - 3248037

Accessories

Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>