

Distribution block - PTFIX 18X1,5 BU - 3002764

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Distribution block, internally jumpered, Connection method: Push-in connection, Number of connections: 18, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 16, Width: 37.8 mm, Height: 17.6 mm, Color: blue, Mounting type: Direct mounting with flange

The illustration shows the version PTFIX 6X1,5 in gray

Your advantages

- ✓ Space-saving, thanks to the compact design
- ✓ Flexible use, thanks to DIN rail and direct mounting
- ✓ Space-saving potential distribution, thanks to compact micro potential distributors
- ✓ Convenient test options, thanks to test openings at every terminal point
- ✓ Clear arrangement thanks to marking of all terminal points

Key commercial data

package_quantity	20
GTIN	4055626432458

Technical data

General

Note	The blocks can be bridged with one another via the conductor shaft. For corresponding plug-in bridges, see accessories
Number of levels	1
Number of connections	18
Potentials	1
Nominal cross section	1.5 mm ²
Color	blue
Insulating material	PA
Flammability rating according to UL 94	V0

General

Rated surge voltage	6 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	0.56 W
Ambient temperature (operation)	-60 °C ... 130 °C
Maximum load current	17.5 A

Distribution block - PTFIX 18X1,5 BU - 3002764

Technical data

General

Nominal current I_N	17.5 A
Nominal voltage U_N	450 V
Open side panel	No

Dimensions

Width	37.8 mm
Length	21 mm
Height	17.6 mm

Connection data

Connection method	Push-in connection
Connection in acc. with standard	IEC 60947-7-1/IEC 60998-1
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	16
Conductor cross section flexible min.	0.14 mm ²
Conductor cross section flexible max.	1.5 mm ²
Min. AWG conductor cross section, flexible	26
Max. AWG conductor cross section, flexible	16
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	1.5 mm ²
Stripping length	8 mm ... 10 mm
Internal cylindrical gage	A1 / B1

Standards and Regulations

Connection in acc. with standard	IEC 60947-7-1/IEC 60998-1
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120

Distribution block - PTFIX 18X1,5 BU - 3002764

Classifications

eCl@ss

eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897
ETIM 6.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

Approval details

CSA ®			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	150 V
Nominal current IN	15 A	15 A	15 A
mm²/AWG/kcmil	26-14	26-14	26-14

UL Recognized			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	150 V
Nominal current IN	15 A	15 A	15 A
mm²/AWG/kcmil	26-14	26-14	26-14

cUL Recognized			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	150 V
Nominal current IN	15 A	15 A	15 A

Distribution block - PTFIX 18X1,5 BU - 3002764

Approvals

Usegroups	B	C	D
mm²/AWG/kcmil	26-14	26-14	26-14

cULus Recognized 
--

Accessories

Screwdriver tools

SZF 0-0,4X2,5 - 1204504



End cover

PTFIX 1,5-DF - 3003116



Jumper

FBS 2-4 - 3030116



FBS 2-4 BU - 3030117



Distribution block - PTFIX 18X1,5 BU - 3002764

Accessories

FBS 2-4 GY - 3030118



End block

CLIPFIX 15 - 3022263



DIN rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



NS 15 AL PERF 2000MM - 1401763

Distribution block - PTFIX 18X1,5 BU - 3002764

Accessories

NS 15 WH PERF 2000MM - 1204096



Labeled terminal marker

SK 4,15/3,8 FORTL.ZAHLEN - 0804378

SK 3,8 REEL P4,15 WH CUS - 0825990

Terminal marking

TML (EX3,8)R - 0801837



TML (104X3,8)R - 0801833



Distribution block - PTFIX 18X1,5 BU - 3002764


Accessories

MPS-MT 1-S4-B RD - 1982800



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>