

Datasheet

Item no. 1573695

V1_0617_01_DT_ds_en

Features

- Choice of various viewing angles
- Low Power consumption
- General purpose leads
- Available on tape and reel.
- Reliable and robust
- The product itself will remain within RoHS compliant version.
- Pb free

Descriptions

- The LED lamps are available with different colors, intensities, epoxy colors, etc

Usage Notes:

- When using LED, it must use a protective resistor in series with DC current about 18mA


Applications

- TV set
- Monitor
- Telephone
- Computer

Device Selection Guide

	Chip		Lens Color
	Material	Emitted Color	
	GaP	Red	Color Diffused

Package Dimensions



UNIT:mm

Notes:

- Other dimensions are in millimeters, tolerance is 0.25mm except being specified.
- Protruded resin under flange is 1.5mm Max LED.
- Bare copper alloy is exposed at tie-bar portion after cutting.

Absolute Maximum Rating (T_a=25°C)

Parameter	Symbol	Absolute Maximum Rating	Unit
Forward Pulse Current	I _{FPM}	100	mA
Forward Current	I _{FM}	30	mA
Reverse Voltage	V _R	5	V
Power Dissipation	P _D	60	mW
Operating Temperature	T _{opr}	-40~+80	°C
Storage Temperature	T _{stg}	-40~+100	°C
Soldering Heat (5s)	T _{sol}	260	°C

Note: *1:Soldering time ≒ 5 seconds.

Electro-Optical Characteristics (T_a=25°C)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Condition
Luminous Intensity	I _v	5	---	10	mcd	IF=20mA(Note1)
Viewing Angle	2θ _{1/2}	---	60	---	Deg	(Note 2)
Peak Emission Wavelength	λ _p	---	640	---	nm	IF=20mA
Spectral Line Half-Width	Δλ	15	20	25	nm	IF=20mA
Forward Voltage	V _F	1.8	---	2.4	V	IF=20mA
Reverse Current	I _R	---	---	10	μA	VR=5V

Note:

1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
2. θ_{1/2} is the off-axis angle at which the luminous intensity is half the axial luminous intensity.

Typical Electro-Optical Characteristics Curves

