

High-current terminal block - PTPOWER 35 BU - 3212065

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



High-current terminal block, Connection method: Power-Turn connection, Number of connections: 2, Cross section: 2.5 mm² - 35 mm², AWG: 12 - 2, Width: 16 mm, Color: blue, Mounting type: NS 35/15

Your advantages

- ✓ Quick and easy connection is now also possible for large conductors with the high-current terminal block
- ✓ The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- ✓ The compact design and front connection enable wiring in a confined space
- ✓ In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection

Key commercial data

package_quantity	10
GTIN	4046356726023

Technical data

General

Number of levels	1
Number of connections	2
Potentials	1
Nominal cross section	35 mm ²
Color	blue
Insulating material	PA
Flammability rating according to UL 94	V0

General

Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Maximum power dissipation for nominal condition	4.06 W
Maximum load current	125 A (with 35 mm ² conductor cross section)
Nominal current I _N	125 A
Nominal voltage U _N	1000 V
Open side panel	No
Relative insulation material temperature index (Elec., UL 746 B)	130 °C

High-current terminal block - PTPOWER 35 BU - 3212065

Technical data

General

Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	16 mm
Length	91.6 mm
Height NS 35/7,5	69.8 mm
Height NS 35/15	77.3 mm

Connection data

Note	Please observe the current carrying capacity of the DIN rails.
Connection method	Power-Turn connection
Conductor cross section solid min.	2.5 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section AWG min.	12
Conductor cross section AWG max.	2
Conductor cross section flexible min.	2.5 mm ²
Conductor cross section flexible max.	35 mm ²
Min. AWG conductor cross section, flexible	12
Max. AWG conductor cross section, flexible	2
Conductor cross section flexible, with ferrule without plastic sleeve min.	2.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	35 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	2.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	35 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	2.5 mm ²

High-current terminal block - PTPOWER 35 BU - 3212065

Technical data

Connection data

2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	10 mm²
Stripping length	25 mm

Standards and Regulations

Flammability rating according to UL 94	V0
---	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120
eCl@ss 9.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897
ETIM 6.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

CSA / BV / UL Recognized / cUL Recognized / LR / DNV GL / cULus Recognized /

Approval details

CSA ®

High-current terminal block - PTPOWER 35 BU - 3212065

Approvals

Usegroups	B	C
Nominal voltage UN	600 V	1000 V
Nominal current IN	115 A	115 A
mm²/AWG/kcmil	14-2	14-2

BV 

UL Recognized 
--

cUL Recognized 	
Usegroups	C
Nominal voltage UN	1000 V
Nominal current IN	115 A
mm²/AWG/kcmil	14-2

LR 

DNV GL

cULus Recognized 

Accessories

Screwdriver tools

SZF 3-1,0X5,5 - 1206612



Jumper

FBS 2-16 - 3005963



Reducing bridge

High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

RB PTPOWER 35-ST(2,5/4) - 3030900



RB PTPOWER 35-ST 16 - 3032170



DIN rail

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

End block

E/AL-NS 35 - 1201662



Terminal marking

TMT (EX9,5)R - 0828295



US-TM 100 - 0829255



ZB 16:UNPRINTED - 0827461



UC-TM 16 - 0819217



High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

UCT-TM 16 - 0829146



ZBF 16:UNPRINTED - 0827464



UC-TMF 16 - 0819262



UCT-TMF 16 - 0829218



Labeled terminal marker

ZB 16 CUS - 0827463



High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

ZB 16,LGS:L1-N,PE - 0827462



UC-TM 16 CUS - 0824621



UCT-TM 16 CUS - 0829637



ZBF 16 CUS - 0827465



UC-TMF 16 CUS - 0824678



UCT-TMF 16 CUS - 0829693



High-current terminal block - PTPOWER 35 BU - 3212065

Accessories

Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>