


Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ground modular terminal block, Connection method: Push-in connection, Number of connections: 4, Cross section: 0.5 mm² - 10 mm², AWG: 20 - 8, Width: 8.2 mm, Height: 42.2 mm, Color: green-yellow, Mounting type: NS 35/7,5, NS 35/15

Your advantages

- ✓ The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- ✓ The compact design and front connection enable wiring in a confined space
- ✓ In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- ✓ Tested for railway applications



Key commercial data

package_quantity	50
GTIN	4046356538145

Technical data

General

Number of levels	1
Number of connections	4
Potentials	1
Nominal cross section	6 mm ²
Color	green-yellow
Insulating material	PA
Flammability rating according to UL 94	V0
Area of application	Railway industry
Area of application	Machine building
Area of application	Plant engineering

General

Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III
Insulating material group	I
Open side panel	Yes

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Technical data

General

Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Oscillation, broadband noise test result	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 2, bogie-mounted
Test frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	$6.12 \text{ (m/s}^2\text{)}^2/\text{Hz}$
Acceleration	3.12 g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Shock test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C
Behavior in fire for rail vehicles (DIN 5510-2)	Test passed
Flame test method (DIN EN 60695-11-10)	V0
Oxygen index (DIN EN ISO 4589-2)	>32 %
NF F16-101, NF F10-102 Class I	2
NF F16-101, NF F10-102 Class F	2
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Dimensions

Width	8.2 mm
End cover width	2.2 mm
Length	90.5 mm
Height	42.2 mm

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Technical data

Dimensions

Height NS 35/7,5	43.5 mm
Height NS 35/15	51 mm

Connection data

Note	Please observe the current carrying capacity of the DIN rails.
Connection method	Push-in connection
Connection in acc. with standard	IEC 60947-7-2
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section AWG min.	20
Conductor cross section AWG max.	8
Conductor cross section flexible min.	0.5 mm ²
Conductor cross section flexible max.	6 mm ²
Min. AWG conductor cross section, flexible	20
Max. AWG conductor cross section, flexible	10
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Stripping length	10 mm ... 12 mm
Internal cylindrical gage	A5

Standards and Regulations

Connection in acc. with standard	CUL
Connection in acc. with standard	IEC 60947-7-2
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
China RoHS	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Classifications

eCl@ss

eCl@ss 5.1	27141118
eCl@ss 6.0	27141141
eCl@ss 7.0	27141141
eCl@ss 8.0	27141141
eCl@ss 9.0	27141141

ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901
ETIM 4.0	EC000901
ETIM 5.0	EC000901
ETIM 6.0	EC000901

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

IECEEx / ATEX / EAC Ex / UL Recognized / cUL Recognized / BV / LR / EAC / CSA / NK / EAC / ABS / VDE approval of drawings /
IECEE CB Scheme / DNV GL / PRS / ABS / GL / cULus Recognized /

Approval details

IECEEx	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.5-6

ATEX 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.5-6

EAC Ex

UL Recognized 
--

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Approvals

Usegroups	B	C
Nominal voltage UN		
Nominal current IN		
mm²/AWG/kcmil	20-8	20-8

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN		
Nominal current IN		
mm²/AWG/kcmil	20-8	20-8

BV 

LR 

EAC 
--

CSA 			
Usegroups	B	C	D
Nominal voltage UN			
Nominal current IN			
mm²/AWG/kcmil	20-8	20-8	20-8

NK ClassNK

ETC

ABS

VDE approval of drawings 	
Nominal voltage UN	1000 V
Nominal current IN	
mm²/AWG/kcmil	0.5-6

IECEE CB Scheme 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.5-6

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Approvals

DNV GL

PRS 

GL 

cULus Recognized 

Accessories

End cover

D-PT 6-QUATTRO - 3212963



Screwdriver tools

SZF 2-0,8X4,0 - 1204520



Documentation

PT-IL - 3208090



Jumper

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

FBS 2-8 - 3030284



FBS 3-8 - 3030297



FBS 4-8 - 3030307



FBS 5-8 - 3030310



FBS 6-8 - 3032470



FBS 10-8 - 3030323



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

FBS 2-8 CT - 3033830



FBS 3-8 CT - 3033831



FBS 4-8 CT - 3033832



FBS 10-8 CT - 3033833



FBS 2-8 BU - 3032567



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

FBS 3-8 BU - 3032570



FBS 4-8 BU - 3032583



FBS 5-8 BU - 3032596



FBS 6-8 BU - 3032677



FBS 10-8 BU - 3032606



FBS 2-8 GY - 3032621



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

FBS 3-8 GY - 3032622



FBS 4-8 GY - 3032635



FBS 5-8 GY - 3032648



FBS 6-8 GY - 3032664



FBS 10-8 GY - 3032651



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

FBSR 2-8 - 3033808



FBSR 3-8 - 3001597



FBSR 4-8 - 3000585



FBSR 5-8 - 3033809



FBSR 10-8 - 3001599



FBSR 16-8 - 3033816



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

Short-circuit connector

FBSRH 2-8 - 3033802



FBSRH 3-8 - 3033803



FBSRH 4-8 - 3033804



Reducing bridge

RB ST 6-(2,5/4) - 3030860



RB ST 6-1,5/S - 3213250



Switching jumper

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

SB-MER 2-8 - 3000587



SB-MER 3-8 - 3000588



SB-MER 4-8 - 3000589



DIN rail

NS 35/ 7,5 PERF 2000MM - 0801733

NS 35/ 7,5 UNPERF 2000MM - 0801681

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

Terminal marking

ZB 8:UNBEDRUCKT - 1052002



UC-TM 8 - 0818072



UCT-TM 8 - 0828740



ZBF 8:UNBEDRUCKT - 0808781



UC-TMF 8 - 0818137



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

UCT-TMF 8 - 0828748



TMT (EX9,5)R - 0828295



US-TM 100 - 0829255



Labeled terminal marker

ZB 8 CUS - 0825011



UC-TM 8 CUS - 0824597



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

UCT-TM 8 CUS - 0829616



ZB 8,LGS:FORTL.ZAHLEN - 1052015



ZB 8,QR:FORTL.ZAHLEN - 1052028



ZB 8,LGS:L1-N,PE - 1052413



ZBF 8 CUS - 0825030



ZBF 8,LGS:FORTL.ZAHLEN - 0808804



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

UC-TMF 8 CUS - 0824654



UCT-TMF 8 CUS - 0829672



Test plug terminal block

MPS-MT - 0201744



PS-8 - 3031005



PS-8/2,3MM RD - 3048564



Insulating sleeve

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

MPS-IH BK - 0201731



Test socket

PAI-4-FIX BU - 3032729



PAI-4-FIX OG - 3034455



PAI-4-FIX YE - 3032745



PAI-4-FIX RD - 3032732



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

PAI-4-FIX GN - 3032758



PAI-4-FIX BK - 3032774



PAI-4-FIX GY - 3032790



PAI-4-FIX VT - 3032761



PAI-4-FIX BN - 3032787



PAI-4-FIX WH - 3032797



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

PAIS-4-FIX GY - 3032791



PAIS-4-FIX BK - 3032792



PAIS-4-FIX RD - 3032793



PAIS-4-FIX BU - 3032798



PAIS-4-FIX YE - 3032799



Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

PAIS-4-FIX GN - 3032801



PAIS-4-FIX VT - 3032802



Partition plate

DP PS-8 - 3036741



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



End block

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Accessories

E/UK - 1201442



E/UK 1 - 1201413



CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276




E/NS 35 N - 0800886



Drawings

Ground modular terminal block - PT 6-QUATTRO-PE - 3212950

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>