

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Highly flexible label, continuous, cassette, yellow with black imprint, mounting type: adhesive, can be marked with THERMOFOX

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 1 |
| GTIN | 4055626212210 |

Technical data

Dimensions

| | |
|-------------------|-------|
| Length (b) | 8 m |
| Width (a) | 12 mm |

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -20 °C ... 75 °C |
| Recommended storage conditions | 20°C/50% relative humidity. Storage in the original packaging is recommended. |

General

| | |
|--|-------------------------------------|
| Color | yellow |
| Components | Free from silicone and cadmium |
| Material | Vinyl polymer |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| RoHS compliant | Yes |
| Adhesive | Acrylic |
| Printability | Thermal transfer |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942

Technical data

General

| | |
|------------------------------|-------------|
| Result | Test passed |
| Marking mounting type | Adhesive |

Standards and Regulations

| | |
|------------------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|------------------------|-----------------------------|

Classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

ETIM

| | |
|-----------------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |

UNSPSC

| | |
|----------------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |

Drawings

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>