



Dimensions	A	B	C	E	F	
Positions	15	39.20	33.30	25.25	19.39	27.70

Dimensions	A±0.15	B±0.10	D±0.13	E±0.08	F±0.10	
Positions	15	39.20	33.30	24.70	19.39	27.70

**NOTES:**

**MATERIAL**

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0
2. Contact Material: Brass or Phosphor Bronze
3. Shell : Steel, 100 μ" Tin Over 50μ" min Copper
4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold & selective 15u"Au

**ELECTRICAL**

1. Current Rating : 3AMP
2. Voltage Rating : 250V AC/rms 60Hz
3. Contact Resistance: 20mΩ
4. Insulation Resistance: 1000MΩ min at 500 VDC
5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute

**ENVIRONMENTAL**

1. Temperature Range: -20°C~+105°C
- UL No. E198287

**NOTES:**

**MATERIAL**

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0, Gray
2. Contact Material: Copper alloy
3. Shell : Steel, 100 μ" Tin Over 50μ" min Copper
- ④ 4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold

**ELECTRICAL**

1. Current Rating : 3AMP
  2. Voltage Rating : 250V AC/rms 60Hz
  3. Contact Resistance: 20mΩ Max at 1 AMP DC
  4. Insulation Resistance: 1000MΩ at 500 VDC
  - ② 5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute
  - ② 6. OPERATING TEMPERATURE: -20°C+105°C
- UL No. E198287

**RoHS compliant**  
Unit:mm