


Marker for terminal blocks - UCT-TM 4 YE - 0828733

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, yellow, unlabeled, can be labeled with: THERMOMARK PRIME, THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, TOPMARK LASER, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

Why buy this product

- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The multi-section marking strips are easy to fit and can be easily separated if required
- ✓ The sheets provide space for including function texts
- ✓ The UCT-TM... UniCard labeling range includes markers for products with tall marker grooves

RoHS

Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 523493
GTIN	4046356523493
Weight per Piece (excluding packing)	13.500 g
Weight per piece (including packing)	15.860 g
Custom tariff number	39269097
Country of origin	Germany
Sales Key	B1 - Marking Assembly
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	10.5 mm
Width (a)	3.6 mm
Height	4.76 mm

Ambient conditions

Marker for terminal blocks - UCT-TM 4 YE - 0828733

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Note	Can be labeled via thermal transfer
Color	yellow
Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	PC
	PC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	84
Number of individual labels per row	14
RoHS compliant	Yes
Printability	Thermal transfer
	Inkjet printing
Device	5146464 THERMOMARK CARD
	5146480 THERMOMARK CARD-UCT-MAG1
	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
	5147421 BLUEMARK FLUID-CARTRIDGE
	5146662 BLUEMARK CLED-FLUID-CARTR.
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	Snap into tall marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190208
------------	----------

Marker for terminal blocks - UCT-TM 4 YE - 0828733

Classifications

eCl@ss

eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-UCT-MAG1 - 5146480



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TM..., UCT1-TM..., UCT5-TM...)

Magazine - TMP-UCT-MAG1 - 0803342



Magazine for the THERMOMARK PRIME printer, for accommodating UCT-TM..., UCT1(U)-TM..., UCT5-TM..., UCT-EM (5x10), UCT-EM (6x10)

