



Dimensions					
Positions	A	B	C	E	F
25	53.08	47.04	40.95	33.24	33.68

Dimensions					
Positions	A	B	C	E	F
25	53.05	47.04	④38.22	33.24	⑥33.68

**Product Specification**

**Material**

Insulator : Glass-Filled Thermoplastic PBT, UL94V-0  
 Contact : Copper alloy

**Electrical**

Contact Resistance : 20 milliohms Max at 1 AMP DC.  
 Insulation Resistance : 1000 megohms at 500 VDC  
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute  
 Current Rating : 3 AMP  
 Voltage Rating : 250 VAC/rms 60Hz  
 ② Wire Spec : 26 AWG~28 AWG  
 Operating Temperature: -55°C ~ +105°C

**Product Specification**

**Material**

Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black  
 Contact : Copper alloy, Gold flash selective gold

**Electrical**

Contact Resistance : 20 milliohmsMax at 1 AMP DC.  
 Insulation Resistance : 1000 megohms at 500 VDC  
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute  
 Current Rating : 3 AMP  
 Voltage Rating : 250 VAC/rms 60Hz  
 ② Wire Spec : 26 AWG~28 AWG  
 Operating Temperature:-55°C+105°C



File No.: E198287

**RoHS compliant**

Unit: mm