


Datasheet

Item no. 1586530

V1_0617_02_EN



NOTES:

Mechanical:

1. Housing material : High Temp. UL94V-0 ,
Color: Black
2. Contact material: Phosphor Bronze $t=0.35\text{mm}$
3. Contact plating: 6u" Gold on contact area
100~200u" Tin on solder area
all over 30~50u" Nickel
4. Shell material: Copper Alloy
5. Shell plating: Nickel plated
6. PCB Retention Pre-solder: 1 LB min.
7. PCB Retention Post-solder: 10 LBS min.



Electrical:

1. Voltage Rating: 125VAC.
2. Current Rating: 1.5AMP.
3. Contact Resistance: 35mΩ max.
4. Insulation Resistance: 1000MΩ min. @ 500 VDC
5. Dielectric Strength: 1000 VAC 60Hz, 1 min.
6. Operation: 750 cycles min.

Environmental:

1. Storage: -40°C To +85°C
2. Operation: -40°C~+85°C
3. Wave Soldering Temperature: 255~265°C(5-10S)

Packing: Tray



File No.: E345352

RoHS compliant

Unit:mm