

Interface module - VIP-3/PT/D25SUB/M - 2903781

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 25-pos.

The illustration shows a 37-position version



Key commercial data

package_quantity	1
GTIN	4046356796569

Technical data

Dimensions

Width	57.1 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. perm. operating voltage	25 V AC
Max. perm. operating voltage	60 V DC
Max. perm. current (per branch)	2 A
Number of positions	25
Status display	No
Mounting position	any

Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	26 ... 14

Interface module - VIP-3/PT/D25SUB/M - 2903781

Technical data

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB pin strip
Number of connections	1
Number of positions	25

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Rated surge voltage	1.2 kV
Degree of pollution	2
Overvoltage category	II

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

CSA / UL Recognized / cUL Recognized / EAC / EAC / EAC / cULus Recognized /

Approval details

CSA ®

Interface module - VIP-3/PT/D25SUB/M - 2903781

Approvals

Nominal voltage UN	105 V
Nominal current IN	2 A
mm ² /AWG/kcmil	26-14

UL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm ² /AWG/kcmil	26-14

cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm ² /AWG/kcmil	26-14

EAC

ERC

ERC

cULus Recognized

Accessories

System cable

CABLE-D25SUB/B/S/ 50/KONFEK/S - 2302120



CABLE-D25SUB/B/S/100/KONFEK/S - 2302133



Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

CABLE-D25SUB/B/S/150/KONFEK/S - 2302146



CABLE-D25SUB/B/S/200/KONFEK/S - 2302159



CABLE-D25SUB/B/S/300/KONFEK/S - 2302162



CABLE-D25SUB/B/S/400/KONFEK/S - 2302175



CABLE-D25SUB/B/S/600/KONFEK/S - 2302188



CABLE D-SUB-S/.../.../... - 2302340



Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

CABLE-D25SUB/B/B/100/KONFEK/S - 2305473



CABLE-D25SUB/B/B/200/KONFEK/S - 2305486



CABLE-D25SUB/B/B/300/KONFEK/S - 2305499



CABLE D-SUB-B-B-S/.../.../... - 2302421



Terminal marking

UC-TM 4 - 0818111



Interface module - VIP-3/PT/D25SUB/M - 2903781

Accessories

UC-TM 6 - 0818085



ZB 5,08:UNBEDRUCKT - 0809793



ZB 22:UNBEDRUCKT - 0811862




Printing system

BLUEMARK X1 - 5147777



Drawings

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>