

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Eight MINI Analog Pro signal conditioners and measuring transducers can be quickly and easily integrated into a Modbus/TCP network via a communication adapter.

Article description

Thanks to its innovative plug-in concept, the communication adapter offers a time-saving wiring solution. Eight MINI Analog Pro signal converters can be quickly and easily integrated into a Modbus/TCP network using a communication adapter. Flexible signal combinations and eliminating the need for I/O input cards saves space and money in the control cabinet.



Key commercial data

package_quantity	1
GTIN	4046356996716

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	51.1 mm
Height	104.1 mm
Depth	61 mm

Supply

Nominal supply voltage range	12 V ... 24 V
Supply voltage range	9.6 V ... 30 V
Typical current consumption	130 mA (at 9.6 V DC)
Power consumption	< 1200 mW

Input data

Available input sources	floating switch contact
Available input sources	Current source
Number of inputs	8
Configurable/programmable	Yes
Current input signal	4 mA ... 20 mA

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Technical data

Input data

Maximum input current	24 mA
Input resistance current input	50 Ω
Maximum input voltage	5 V

Output data

Number of outputs	1
Configurable/programmable	Yes
Transmission speed	10 Mbps
Transmission speed	100 Mbps
Data update rate	15 ms

General

Maximum transmission error	0.1 %
Maximum temperature coefficient	0.01 %
Degree of protection	IP20 (Finger safety)
Overvoltage category	II
Degree of pollution	2
Rated insulation voltage	50 V _{rms}
Test voltage, input/output/supply	0.5 kV
Status display	Green LED
Indication	Red LED
Housing material	PBT 7% GF V0
Mounting position	any

Connection data

Connection name	Output
Connection method	RJ45
Number of positions	8

Ambient conditions

Ambient temperature (operation)	-40 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 %
Permissible humidity (storage/transport)	5 % ... 95 %
Maximum altitude	4000 m

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC directive
Noise emission	EN 61000-6-4
Conformance	CE-compliant
UL, USA/Canada	UL 508 Listed
UL, USA/Canada	Class I, Div. 2, Groups A, B, C, D T5
UL, USA/Canada	Class I, Zone 2, Group IIC T5
GL	GL applied for

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.1	27242608
eCl@ss 6.0	27242608
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608
eCl@ss 9.0	27242608

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604
ETIM 6.0	EC001604

UNSPSC

UNSPSC 13.2	32151602
--------------------	----------

Approvals

UL Listed / cUL Listed / cULus Listed / UL Listed / cUL Listed / cULus Listed /

Approval details

UL Listed

cUL Listed

cULus Listed

--

--

--

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

DIN rail connector

ME 6,2 TBUS-2 1,5/5-ST-3,81 GN - 2869728



Power module

MINI MCR-2-PTB - 2902066



MINI MCR-2-PTB-PT - 2902067



Feed-through terminal block

MINI MCR-2-TB - 2902068



MINI MCR-2-TB - 2902068



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

Evaluation unit

MINI MCR-2-FM-RC - 2904504



MINI MCR-2-FM-RC-PT - 2904508



MINI MCR-2-FM-RC - 2904504



MINI MCR-2-FM-RC-PT - 2904508



Programming adapter

IFS-BT-PROG-ADAPTER - 2905872



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

IFS-USB-PROG-ADAPTER - 2811271



NFC-USB-PROG-ADAPTER - 2900013



Device marking

UCT-EM (30X5) - 0801505



UCT-EM (30X5) YE - 0830340



UC-EMLP (15X5) - 0819301



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

UC-EMLP (15X5) YE - 0822615



UC-EMLP (15X5) SR - 0828095



US-EMLP (15X5) - 0828790



US-EMLP (15X5) YE - 0828873



US-EMLP (15X5) SR - 0828874



Labeled device marker

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

UCT-EM (30X5) CUS - 0801589



UCT-EM (30X5) YE CUS - 0830348



UC-EMLP (15X5) CUS - 0824550



UC-EMLP (15X5) YE CUS - 0824551



UC-EMLP (15X5) SR CUS - 0828099



US-EMLP (15X5) CUS - 0830076



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

US-EMLP (15X5) YE CUS - 0830077



US-EMLP (15X5) SR CUS - 0830078



Terminal marking

SK 5,0 WH:REEL - 0805221



Signal conditioner

MINI MCR-2-UNI-UI-UIRO-PT - 2902028



MINI MCR-2-UNI-UI-UIRO - 2902026



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-UNI-UI-UIRO-PT-C - 2902027



MINI MCR-2-UNI-UI-UIRO-C - 2902024



MINI MCR-2-UI-UI-PT - 2902040



MINI MCR-2-UI-UI - 2902037



MINI MCR-2-UI-UI-PT-C - 2902039



MINI MCR-2-UI-UI-C - 2902036



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-U-UI-PT - 2902021



MINI MCR-2-U-UI - 2902019



MINI MCR-2-U-I0-PT - 2902023



MINI MCR-2-U-I0 - 2902022



MINI MCR-2-U-I4-PT - 2902030



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-U-I4 - 2902029



MINI MCR-2-I-I-PT - 2901999



MINI MCR-2-I-I - 2901998



MINI MCR-2-I-I-ILP-PT - 2901995



MINI MCR-2-I-I-ILP - 2901994



Signal duplicator

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-UNI-UI-2UI-PT - 2905028



MINI MCR-2-UNI-UI-2UI - 2905026



MINI MCR-2-UNI-UI-2UI-PT-C - 2905027



MINI MCR-2-UNI-UI-2UI-C - 2905025



Repeater power supplies

MINI MCR-2-RPSS-I-I-PT - 2902015



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-RPSS-I-I - 2902014



MINI MCR-2-RPSS-I-2I-PT - 2905629



MINI MCR-2-RPSS-I-2I - 2905628

Temperature transmitter

MINI MCR-2-RTD-UI-PT - 2902052



MINI MCR-2-RTD-UI - 2902049



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-RTD-UI-PT-C - 2902051



MINI MCR-2-RTD-UI-C - 2902048



MINI MCR-2-TC-UI-PT - 2905249



MINI MCR-2-TC-UI - 2902055



MINI MCR-2-TC-UI-PT-C - 2905248



MINI MCR-2-TC-UI-C - 2902053



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

Threshold value switch

MINI MCR-2-T-REL-PT - 2905633



MINI MCR-2-T-REL - 2905632



Frequency transducer

MINI MCR-2-UI-FRO-PT - 2902032



MINI MCR-2-UI-FRO - 2902031



MINI MCR-2-UI-FRO-PT-C - 2906202



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-UI-FRO-C - 2906201



MINI MCR-2-F-UI - 2902056



MINI MCR-2-F-UI-PT - 2902058



Potiposition transducer

MINI MCR-2-POT-UI-PT - 2902017



MINI MCR-2-POT-UI - 2902016



Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Accessories

MINI MCR-2-POT-UI-PT-C - 2905006



MINI MCR-2-POT-UI-C - 2905005



Isolating switch transf.

MINI MCR-2-NAM-2RO-PT - 2902005



MINI MCR-2-NAM-2RO - 2902004



Accessories


ME 6,2 TBUS-2 1,5/5-ST-3,81 GY - 2695439



Drawings

Communication module - MINI MCR-2-V8-MOD-TCP - 2905635

Block diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>