

Data Sheet

FRONT VIEW DIMENSIONS:
 *30.5^{+0.3}/_{-0.15}
 *24.0^{+0.5}/₋₀
 14.0±0.2
 2.0±0.05
 *16.0^{+0.5}/₋₀
 4.0±0.2
 *50.0^{+0.3}/_{-0.2}
 4-R3.5

CROSS SECTION DIMENSIONS:
 17.0^{+1.0}/₋₀
 *15.0^{+0.5}/₋₀
 *12.0^{+1.0}/₋₀
 4.0±0.1
 0.8t

REAR VIEW DIMENSIONS:
 *28.0
 27.5
 *46.8^{+0.5}/_{-0.2}
 RICH BAY R-3014S
 Max 12.5W
 10A 250V

PANEL CUT-OUT DIMENSIONS:
 47.0^{+0.4}/₋₀
 4-R2
 27.6±0.2

SWITCH DIMENSIONS:
 *A^{+0.2}/₋₀
 3.0
 19.5
 (30.5)
 4.8

TABLE:

	XX	A
	10	1.0
	15	1.5
	20	2.0

SPECIFICATION: (SWITCH)

1. Electrical rating : 6A 250VAC & 12A 125VAC [UL]
4(1)A 250VAC [VDE . ENEC10]
2. Contact resistance : <20mΩ (Initial)
3. Insulation resistance : 100MΩ (500VDC between open contacts)
4. Dielectric strength : 1500V 1 minute

SPECIFICATION:

1. Insulation Resistance: Over 100MΩ at 500V DC.
2. Dielectric strength: 2000V AC 1 Minute.
3. Body Material: Thermoplastic 94V-2~V-0.

Rating:AC 15A 250V	
Mark	Safety Regulation
	CULUS
Rating:AC 10A 250V	
Mark	Safety Regulation
	VDE
	ENEC

UNIT mm DRAWN BY	UNIT Q'TY 1 APPROVED BY	SCALE 1:1	TOLERANCE X.XX±0.1 XX.XX±0.2 XXX.XX±0.3	PRODUCT NO.	R-3014S (01) XX	REV
		ID NO	210218A10	INTERIM NO.		
		DESCRIPTION		NEW NO.		