



## Hi-Speed USB B Data + Charging Cable

USB 2.0, Type-A Male to Type-B Male, 480 Mbps, 0.5 m (1.5 ft.), Black

Part No.: [374507](#)

EAN-13: 0766623374507 | UPC: 766623374507

Quality connections for superior performance.

Manhattan Hi-Speed USB (Full Speed USB) Device Cables easily connect computers and USB-powered peripherals like printers, scanners, external enclosures and an expanding assortment of digital devices. Manhattan Hi-Speed USB Device Cables are engineered and constructed of quality materials that support data transfer rates up to 480 Mbps to deliver dependable, error-free transmissions. Full foil and braided shielding, gold-plated contacts and molded boots with strain relief assure maximum conductivity to quickly connect USB-enabled devices, reduce EMI interference and minimize data degradation.

### Features:

- USB 2.0 Type-A male to Type-B male
- Connects a Hi-Speed USB device to a Hi-Speed USB hub or computer
- Supports speeds of up to 480 Mbps
- Hi-Speed USB for ultra-fast data-transfer rates with zero data degradation
- Lifetime Warranty

### Specifications:

#### Standards and Certifications

- UL 2725
- USB 2.0

For more information on Manhattan products, consult your local dealer or visit [www.manhattan-products.com](http://www.manhattan-products.com).

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

#### Connectors

- One USB 2.0 Type-A male
- One USB 2.0 Type-B male
- Gold plated contacts
- Molded PVC boot with strain relief

#### Cable

- Shielded
- Current rating: 0.5 ADC
- Withstanding voltage: 300 VDC
- Insulation resistance: 5 MOhm
- Conductive resistance: 5 Ohm
- Thermal plastic casing
- 28 AWG conductors

#### Physical

- Length: 0.5 m (1.5 ft.)
- Weight: 24 g (0.9 oz.)

#### Operating Environment

- Operation temperature: 0 - 50°C (32 - 122°F)
- Storage temperature: -25 - 85°C (-13 - 185°F)
- Humidity (noncondensing): 0 - 96%

#### Package Contents

- Hi-Speed USB Device Cable



