


## Standard TEC module, 25x25x3.6mm



Max Operating Temperature: 90°C.

## Datasheet

Item no. 1569028

V1\_07312018\_01\_en

Hot Side Temperature(°C)	25 °C	50 °C
Qmax (Watts)	18.1	19.1
Delta Tmax(°C)	67	75
I <sub>max</sub> (Amps)	2.1	2.1
V <sub>max</sub> (Volts)	15.4	16.4
Module Resistance(Ohms)	6.34	7.15


\*\*Tolerances for thermal and electrical parameters  $\pm 10\%$ .

# Datasheet

Item no. 1569028

V1\_07312018\_01\_en

Performance Curves Th=25 °C



Performance Curves Th=50 °C

