

TDE Instruments GmbH  
 Gewerbestraße 8  
 D-71144 Steinenbronn  
 Germany

Tel.: +49(0)7157 20801  
 Fax: +49(0)7157 20813  
 Email: info@tde-instruments.de  
 Web: www.digalox.com



## Digalox DPM72-MP

Graphical DIN-panelmeter for voltage, ampere and power with multiple display, RGB backlight and USB interface

### Description


Graphical measuring instrument which unites the benefits of an analogue display with the accuracy of a digital instrument. The multi display with RGB backlight is able to display up to 4 parameters simultaneously. Thresholds can be associated with individual warning backlight colors. A variety of measure modes (volt AC/DC, ampere, frequency, power, cos phi) are supported. Scale endpoint of the indicator as well as scaling of the analogue signal and current transformer measurement can be adjusted freely via the DIP switch, alternatively there is an option for automatic adaption of the scale endpoint. The unit can be switched between measurement modes via an external switch. Minimum and maximum values for each parameter are recorded and can be displayed optionally

using an external switch. Measured values of one parameter are recorded over a timespan of 3 minutes up to 14 days. The timebase as well as the display of the measuring history can be activated by an external switch. The following parameters can be adjusted using the USB-Software: Scale endpoint, scale caption, display style (pointer, tachometer, bargraph, and more), splash display, backlight color, thresholds for alarm output, threshold warning color (light, blink), hysteresis, and more. Recorded measurement values can be read and a continuous transmission up to four measuring values can be enabled. Using the software, values can be viewed and exported as CSV.

### Features

- Graphic display 16 grey levels with RGB backlight
- Pointer and digital display
- Multi display of up to 4 parameters
- USB interface, galvanically isolated
- Adjustable scale endpoint
- Recording of measurement over up to 14 days
- Alarm outputs with adjustable thresholds, galvanically isolated
- Individual alarm backlight color
- User splash display
- Different display styles, e.g. tachometer, bargraph, timebased view
- Transmission of measure value
- Integration of measure value
- Accuracy 1% true RMS
- Windows software for individual configuration and measure value recording

### Samples adjustable display styles






TDE Instruments GmbH  
 Gewerbestraße 8  
 D-71144 Steinenbronn  
 Germany

Tel.: +49(0)7157 20801  
 Fax: +49(0)7157 20813  
 Email: info@tde-instruments.de  
 Web: www.digalox.com

## Software

The corresponding free software enables the individual configuration of the meter. Via software the measured value can be read from the memory, as well as continuous data transmission enabled.

Using the software, values can be viewed, recorded and be exported as CSV.



## Spezifikation

### Supply:

10-24V AC/DC, galvanically isolated

### Display:

LCD graphic display 192x160 pixels

### Measuring range voltage:

AC 0-500V

DC +/- 500V

### Accuracy voltage:

1%

### Measuring range ampere:

AC 0-10A

AC 5A for current transformer

DC +/-10A

### Accuracy ampere:

1%

### Measuring range frequency:

10-500Hz

### Accuracy frequency:

0,1Hz

### Recording of measurement:

3 min to 14 days

### Alarm outputs:

2 optocouple outputs max. 30V, 50mA

### Operating temperature:

0°C to +50°C

### Storage temperature:

-20°C bis +70°C

### Front panel:

72 mm x 72 mm

### Panel cut out:

68 mm x 68 mm

### Fixation:

Bracket

### Protection front:

IP65 with gasket (separate available)

## Other Instruments of Digalox DPM72 series


### Digalox DPM72-AV

Graphical DIN-panelmeter for Voltage and Ampere.



### Digalox DPM72-AVP

Graphical DIN-panelmeter for Voltage and Ampere with USB interface.



### Digalox DPM72-PP

Graphical DIN-panelmeter for DC shunt measurement and analog signal with USB interface.

