


Data Sheet

R2 Tube and sleeve - blister pack



Product Dimensions

Part Number	Size(mm)	As supplied (mm)		After recovered (mm)		Length
		I.D.(D)	W.T.(W)	I.D.(max)(d)	W.T.(min)(w)	
R2-0200	20.0 (3/4")	21.0±0.5	0.40±0.10	10.0	0.77	2M/Per blister pack

**Blister Pack Size(dia.): 9.5cm

Technical Data

Property	Specification Requirement	Test Method	Typical Value
Longitudinal change	-10%~10%	ASTM D2671	Pass
Tensile strength	≥10.3MPa	ASTM D638	≥11.3MPa
Elongation at break	≥200%	ASTM D638	≥400%
Tensile strength after aging	70% of initial value	ASTM D638 (158°C/168 hrs)	≥80%
Elongation at break after aging	≥100%	ASTM D638 (158°C/168 hrs)	≥200%
Heat shock	No cracking	ASTM D2671 (200°C/4 hrs)	No cracking
Low temperature flexibility	No cracking	ASTM D2671 (-30°C/1 hr)	No cracking
Dielectric voltage withstand	AC2500V/60S No breakdown	ASTM D2671	No breakdown
Volume resistivity	≥10 ¹⁴ Ω · cm	ASTM D876	≥10 ¹⁴ Ω · cm
Dielectric strength	≥19.7kV/mm	ASTM D2671	22 kV/mm
Flammability	VW-1	UL224	Pass