



## Solderless Breadboard



Tolerance: ±0.2mm

### Swpe

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau ([www.conrad.com](http://www.conrad.com)).  
 All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

# Datasheet

Item no. 1572580

V1\_10022018\_01\_en

---

## Specifications

Material: .....ABS Plastic  
Heat Distortion Temperature: .....84°C  
Spring Clip Contact: .....Phosphor Bronze  
Finish: .....Nickel Plated  
Insertion Range: .....Ø 0.4-0.7 mm  
400 Tie-Point  
Board Size: .....86.5 x 64.5 x 8.5 mm