

Preliminary

TX-BRPG2B140-001

DATA SHEET

Approved by:

Part No.

Checked by:

Spec No.

TX-BRPG2B140-001

Prepared by:

Page

WKF-BB2026

1 of 7




Features:


- ◆ Excellent Transiting Heat from LED Chip Operating under 500mA
- ♦ High Luminous Output
- ◆ No UV

Typical purpose:

- ◆ Portable Flashlight
- ◆ Garden lighting
- ♦ General Lighting

Package Dimensions:





Part No.	TX-BRPG2B140-001	Spec No.	WKF-BB2026	Page	2 of 7
----------	------------------	----------	------------	------	--------



Notes:

- 1. Thermoelectric integrated Red chip packaged in this product.
- 2.All dimensions are in millimeters (inches).
- 3. Tolerance is ± 0.25 mm (0.01") unless otherwise noted.

Part NO.	Chip Material				Lens Color	
TX-BRPG2B140-001	140-001 Blue	Red	Purple	Green	Water Clear	Blue & True Red
1 A-DKI 02D140-001	GaInN	AlGaInP	GaInN	GaInN	water Clear	Blue & True Red &Purple & Green

Absolute Maximum Ratings at Ta=25℃

Parameter	Symbol	MAX.	Unit
LED Junction Temperature	Tj	150	$^{\circ}$
XIO	В	1800	16
Power Dissipation	P _D R	1300	mW
Tower Dissipation	р	1800	IIIVV
⊗	G	1800	1
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	I_{FP}	1000	mA
Continuous Forward Current	IF	500	mA
Reverse Voltage	V _R	5	V
ElectrostaticDischarge Threshoid (ESD)	ESD	2000	V
Operating Temperature Range	Topr	-40 to +70	°C
Storage Temperature Range	T _{spr}	-40 to +100	
7			

Notes:

- 1. Specifications are subject to change without notice.
- 2. Under the stipulated Characteristics parameters above, the life span of the LED is more than 50,000hours.
- 3. The data on this specification is for reference only and the actual data is in accordance with the acknowledgment.
- 4. Precautions for ESD:

STATIC SHIELD Electricity and surge damages the LED. It is recommended to use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.

Part No.	TX-BRPG2B140-001	Spec No.	WKF-BB2026	Page	3 of 7
----------	------------------	----------	------------	------	--------



Characteristics at If=500mA, Vr=5V (Ta=25°C)

			. ()	y		
Parameter	Symbol	Emitting Values			Units	
Parameter	Symbol	Color	Min.	Тур.	Max.	Units
X		В	25	35		^
I San and Elmi	Фу	R	70	85		lm
Luminous Flux		P	1	2		
® \\		G	115	145	,1	8,
, int		В		140	⊗ — <	,
Viewing Angle at 50% IV	$2\theta_{1/2}$	R		140 <	A Ta	Dan
Viewing Angle at 30 % IV	201/2	P		140	H allin	Deg
		G		140	Hr.	
		В	450	452.5	455	nm
Peak Emission Wavelength) n	R	625 .x	4 630	635	
reak Elilission wavelength	λр	P	395	400	405	
160		G	510	515	520	
, O _C ,	λd	В	458	461	464	nm
Dominant Wavelength		R _x O	620	625	630	
Dominant wavelength		P	380	390	400	
		G	522	525	528	K
*	$\triangle \lambda$	В	15	20	25 🔟	nm
Spectral Line Half-Width		R	15	20	© 25 \	
and Francisco Victor		P	15	20 <	25	
	Han	G	25	30	35	
	$V_{ m f}$	В	3.0	3.3	3.6	V
Forward Voltage		R	2.0	2.3	2.6	
1 of ward voltage	, , ,	P	3.0	3.3	3.6	
		G	3.0	3.3	3.6	
Reverse Current	I_R	_	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\		10	μA
Thermal Resistance Junction to Case	$R\theta_{J-C}$	_ <	_	15		K/W
Temperature Coefficient of Forward Voltage	V△F/T	2 to 10		-2	_	mV/℃


Notes:


- 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- $2.\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity
- 3. The dominant wavelength (λd) is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.
- 4. Flux is measured with an accuracy of $\pm 15\%$.
- 5. Forward voltage is measured with an accuracy of ± 0.15 V.





Typical Electrical / Optical Characteristics Curves


(25°C Ambient Temperature Unless Otherwise Noted)











 Part No.
 TX-BRPG2B140-001
 Spec No.
 WKF-BB2026
 Page
 5 of 7

380 400 420 440 460 480 500 520 540 560 580 600 620 640 660 680 700 720 740 760 780 Wave Length (nm)



PRECAUTION IN USE

Storage


Recommended storage environment

Temperature: 5° C ~ 30° C (41oF ~ 86oF)

Humidity: 60% RH Max.

Soldering

Use the conditions shown to the under figure.



Profile Feature	Lead-Based Solder		
Average Ramp-Up Rate (Ts _{max} to T _p)	3°C/second max. ○		
Preheat: Temperature Min (Ts _{min})	100℃		
Preheat: Temperature Max (Ts _{max})	150°C		
Preheat: Time (Ts _{min} to Ts _{max})	60-120 seconds		
Time Maintained Above: Temperature (T _L)	183℃		
Time Maintained Above: Time (T _L)	60-150 seconds		
Peak/Classification Temperature (T _P)	215℃		
Time Within 5°C of Actual Peak Temperature (T _P)	10-30 seconds		
Ramp-Down Rate	6°C/second max.		
Time 25°C to Peak Temperature	6 minutes max.		


Note: All temperatures refer to topside of the package, measured on the package body surface.

Part No.	TX-BRPG2B140-001	Spec No.	WKF-BB2026	Page	6 of 7
----------	------------------	----------	------------	------	--------



Dimensions for Cannulation and Packaging

Quantity: 40PCS



Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ± 2.0 mm (0.08") unless otherwise noted.
- 3. The products are packaged together with silica gel, Transport, not to the weight of welding LED light-emitting area, As a result of the weight of LED light-emitting zone in the quality of, Irresponsible of the Company.