



VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."

CNPS-45 C€

COMPACT USB-C POWER ADAPTER

Nº 1601915

This product is designed to charge and power compatible USB-C[™] devices. Power is supplied via a standard household mains socket. The product is protected against overloads and short circuits. It automatically recognizes the charging parameters using Power Delivery technology, enabling quick and efficient charging for a range of different devices.

This product is intended for indoor use only. Do not use it outdoors. Contact with moisture (e.g. in bathrooms) must be avoided under all circumstances.

HIGHLIGHTS

USB power delivery up to 20 V / 45 W //

Built-in circuit automatically detects the charging specifications //

Overload protection //

TECHNICAL DATA

Input voltage/current100–240 V/AC, 50/60 Hz, max. 1 AOutput voltages/currents5 V/DC, 9 V/DC, 12 V/DC, 15 V/DC / 3 A; 20 V/DC, 2.25 APowerMax. 45 W (overload protection up to max. 55 W)Surge protection5/9/12 V up to max. 3.9 A; 20 V up to max. 2.9 ARipple220 mV p-p max.USB typeUSB-C™Efficiency classLevel VI
Power Max. 45 W (overload protection up to max. 55 W) Surge protection 5/9/12 V up to max. 3.9 A; 20 V up to max. 2.9 A Ripple 220 mV p-p max. USB type USB-C™
Surge protection5/9/12 V up to max. 3.9 A; 20 V up to max. 2.9 ARipple220 mV p-p max.USB typeUSB-C™
Ripple 220 mV p-p max. USB type USB-C™
USB type USB-C™
7,50
Efficiency class Level VI
Colour Black
Operating conditions 0 to +35 °C, 10–95 % relative humidity (non-condensing
Storage conditions -10 to +55 °C, 5–95 % relative humidity (non-condensing
Dimensions (W x H x D) 94 x 56 x 28 mm
Weight 116 g



VERSION 12/21

PACKAGE CONTENT

USB power adapter // USB-C™ cable // Operating instructions //

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.