

Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pre-assembled solid-state relay module with screw connection, consisting of: relay base with ejector and plug-in miniature solid-state relay. Input voltage: 24 V DC. Output: 3 - 33 V DC/3 A



Key commercial data

package_quantity	10
GTIN	4046356983488

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	6.2 mm
Height	84 mm
Depth	68 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Coil side

Power dissipation for nominal condition	0.2 W
---	-------

Connection data input side

Connection name	Input side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.5 mm ² ... 4 mm ²
Conductor cross section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross section AWG	20 ... 12
Torque	0.5 Nm

Connection data output side

Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Technical data

Connection data output side

Connection name	Output side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.5 mm ² ... 4 mm ²
Conductor cross section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.5 mm ² ... 2.5 mm ² (Ferrules without plastic sleeve)
Conductor cross section flexible	0.5 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve)
Conductor cross section AWG	20 ... 12
Torque	0.5 Nm

General

Operating mode	100% operating factor
Degree of protection	IP20
Mounting position	any
Assembly instructions	In rows with zero spacing

Standards and Regulations

Designation	Air clearances and creepage distances between the power circuits
Standards/regulations	DIN EN 50178
Rated insulation voltage	260 V AC
Rated surge voltage	4 kV
Insulation	Basic insulation
Degree of pollution	2
Overvoltage category	III

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371604
eCl@ss 7.0	27371604
eCl@ss 8.0	27371604
eCl@ss 9.0	27371604

ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504

Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Classifications

ETIM

ETIM 5.0	EC001504
ETIM 6.0	EC001504

UNSPSC

UNSPSC 13.2	39122326
--------------------	----------

Accessories

End block

CLIPFIX 35 - 3022218



Test plug terminal block

MPS-MT - 0201744



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



Terminal marking

Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Accessories

ZB 6:UNBEDRUCKT - 1051003



Jumper

FBS 2-6 - 3030336



FBS 3-6 - 3030242



FBS 4-6 - 3030255



FBS 5-6 - 3030349



Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Accessories

FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



FBS 2-6 BU - 3036932



FBS 3-6 BU - 3036945



FBS 4-6 BU - 3036958



Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Accessories

FBS 5-6 BU - 3036961



FBS 10-6 BU - 3032198



FBS 20-6 BU - 3032208



FBS 50-6 BU - 3032211



FBS 2-6 GY - 3032237



Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Accessories

FBS 3-6 GY - 3032240



FBS 4-6 GY - 3032279



FBS 5-6 GY - 3032266




FBS 10-6 GY - 3032253




Drawings

Diagram



Solid-state relay module - RIF-0-OSC-24DC/24DC/2 - 2905657

Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>