

Safety Data Sheet

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- 1.1. Product identifier
Mixture identification:
Trade name: 106 EcoTank Photo Black ink bottle, T00R1
- 1.2. Relevant identified uses of the substance or mixture and uses advised against
Recommended use:
Ink for inkjet printing
- 1.3. Details of the supplier of the safety data sheet
Company:
EPSON EUROPE B.V.
Azie building, Atlas ArenA, Hoogoorddreef 5, 1101 BA Amsterdam
Zuidoost The Netherlands
Phone number: +31-20-314-5000
Competent person responsible for the safety data sheet:
chemicals@epson-europe.com
Date: 23/06/2017
Revision: 2.0
- 1.4. Emergency telephone number
Phone number: +31-20-314-5000
United Kingdom; 01952 607111 Monday to Friday 9am to 5:30pm.
Emergency Action: In the event of a medical enquiry involving this product, please contact your doctor or local hospital accident and emergency department.

SECTION 2: Hazards identification

- 2.1. Classification of the substance or mixture
EC regulation criteria 1272/2008 (CLP)
The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
Adverse physicochemical, human health and environmental effects:
No other hazards
- 2.2. Label elements
The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
Hazard pictograms:
None
Hazard statements:
None
Precautionary statements:
None
Special Provisions:
EUH210 Safety data sheet available on request.
EUH208 Contains 1,2-benzisothiazol-3(2H)-one; 1,2-benzisothiazolin-3-one. May produce an allergic reaction.
Special provisions according to Annex XVII of REACH and subsequent amendments:
None
- 2.3. Other hazards
vPvB Substances: None - PBT Substances: None
Other Hazards:
No other hazards







SECTION 3: Composition/information on ingredients

- 3.1. Substances
No

Safety Data Sheet

3.2. Mixtures

Hazardous components within the meaning of the CLP regulation and related classification:

Qty	Name	Ident. Number	Classification
65% ~ 80%	Water	CAS: 7732-18-5 EC: 231-791-2	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
7% ~ 10%	Glycerol	CAS: 56-81-5 EC: 200-289-5	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
7% ~ 10%	2-[2-(2-butoxyethoxy)ethoxy]ethanol; TEGBE; triethylene glycol monobutyl ether	Index number: 603-183-00-0 CAS: 143-22-6 EC: 205-592-6 REACH No.: 01-21194751 07-38	 3.3/1 Eye Dam. 1 H318
1% ~ 3%	E-BK105	EC: 700-794-5 REACH No.: 01-21199285 35-33	4.1/C3 Aquatic Chronic 3 H412
0.1% ~ 0.25%	Triethanol amine	CAS: 102-71-6 EC: 203-049-8	The product is not classified as dangerous according to Regulation EC 1272/2008 (CLP).
< 0.05%	1,2-benzisothiazol-3(2H)-one; 1,2-benzisothiazolin-3-one	Index number: 613-088-00-6 CAS: 2634-33-5 EC: 220-120-9	 3.1/4/Oral Acute Tox. 4 H302  3.2/2 Skin Irrit. 2 H315  3.3/1 Eye Dam. 1 H318  3.4.2/1-1A-1B Skin Sens. 1,1A,1B H317  4.1/A1 Aquatic Acute 1 H400

SECTION 4: First aid measures

4.1. Description of first aid measures

In case of skin contact:

Wash with plenty of water and soap.

In case of eyes contact:

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

In case of Ingestion:

Do not under any circumstances induce vomiting. OBTAIN A MEDICAL EXAMINATION IMMEDIATELY.

In case of Inhalation:

Remove casualty to fresh air and keep warm and at rest.

4.2. Most important symptoms and effects, both acute and delayed

None

4.3. Indication of any immediate medical attention and special treatment needed

Treatment:

None

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Water.

Safety Data Sheet

Carbon dioxide (CO₂).

Extinguishing media which must not be used for safety reasons:

None in particular.

5.2. Special hazards arising from the substance or mixture

Do not inhale explosion and combustion gases.

Burning produces heavy smoke.

5.3. Advice for firefighters

Use suitable breathing apparatus .

Collect contaminated fire extinguishing water separately. This must not be discharged into drains.

Move undamaged containers from immediate hazard area if it can be done safely.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear personal protection equipment.

Remove persons to safety.

See protective measures under point 7 and 8.

6.2. Environmental precautions

Do not allow to enter into soil/subsoil. Do not allow to enter into surface water or drains.

Retain contaminated washing water and dispose it.

In case of gas escape or of entry into waterways, soil or drains, inform the responsible authorities.

Suitable material for taking up: absorbing material, organic, sand

6.3. Methods and material for containment and cleaning up

Wash with plenty of water.

6.4. Reference to other sections

See also section 8 and 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid contact with skin and eyes, inhalation of vapours and mists.

Do not eat or drink while working.

See also section 8 for recommended protective equipment.

7.2. Conditions for safe storage, including any incompatibilities

Keep away from food, drink and feed.

Incompatible materials:

None in particular.

Instructions as regards storage premises:

Adequately ventilated premises.

7.3. Specific end use(s)

None in particular

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Glycerol - CAS: 56-81-5

- OEL Type: OSHA - LTE: 5 mg/m³

- OEL Type: OSHA - LTE: 15 mg/m³

DNEL Exposure Limit Values

No data available

PNEC Exposure Limit Values

2-[2-(2-butoxyethoxy)ethoxy]ethanol; TEGBE; triethylene glycol monobutyl ether -

CAS: 143-22-6

Target: Fresh Water - Value: 1.5 mg/l

Target: Freshwater sediments - Value: 5.77 mg/kg

Safety Data Sheet

Target: Marine water - Value: 0.15 mg/l
Target: Marine water sediments - Value: 0.13 mg/kg
Target: Microorganisms in sewage treatments - Value: 200 mg/l

8.2. Exposure controls

8.2.1. Appropriate engineering controls:
None

8.2.2. Individual protection measures, such as personal protective equipment

Eye protection:

Not needed for normal use. Anyway, operate according good working practices.

Protection for skin:

No special precaution must be adopted for normal use.

Protection for hands:

Not needed for normal use.

Respiratory protection:

Not needed for normal use.

Thermal Hazards:

None

8.2.3. Environmental exposure controls:

None

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance and colour:	Black Liquid
Odour:	Slightly
Odour threshold:	No data available
pH:	8 ~ 9 at 20 °C
Melting point / freezing point:	-15.6 °C
Initial boiling point and boiling range:	No data available
Solid/gas flammability:	No data available
Upper/lower flammability or explosive limits:	No data available
Vapour density:	No data available
Flash point:	Does not flash until 100 °C / 212 ° F (closed cup method, ASTM D 3278)
Evaporation rate:	No data available
Vapour pressure:	No data available
Relative density:	1.059 at 20 °C
Solubility in water:	Complete
Solubility in oil:	No data available
Partition coefficient (n-octanol/water):	No data available
Auto-ignition temperature:	No data available
Decomposition temperature:	No data available
Viscosity:	< 5 mPa·s at 20 °C
Explosive properties:	No data available
Oxidizing properties:	No data available

9.2. Other information

Miscibility:	No data available
Fat Solubility:	No data available
Conductivity:	No data available

SECTION 10: Stability and reactivity

10.1. Reactivity

Stable under normal conditions

10.2. Chemical stability

Stable under normal conditions

Safety Data Sheet

- 10.3. Possibility of hazardous reactions
None
- 10.4. Conditions to avoid
Stable under normal conditions.
- 10.5. Incompatible materials
None in particular.
- 10.6. Hazardous decomposition products
None.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological information of the mixture:

e) germ cell mutagenicity:

Test: Mutagenesis - Species: Salmonella Typhimurium and Escherichia coli
Negative

f) carcinogenicity:

Does not contain carcinogens (Ref. 1)

g) reproductive toxicity:

Does not contain reproductive toxicity and developmental toxic substances (Ref. 2)

Toxicological information of the main substances found in the mixture:

Glycerol - CAS: 56-81-5

a) acute toxicity:

Test: LD50 - Route: Oral - Species: Guinea pig = 7750 mg/kg - Source: Journal of Industrial Hygiene and Toxicology. Vol. 23, Pg. 259, 1941

Test: LDLo - Route: Oral - Species: Human = 1428 mg/kg - Source: "Toxicology of Drugs and Chemicals," Deichmann, W.B., New York, Academic Press, Inc., 1969Vol. -, Pg. 288, 1969.

2-[2-(2-butoxyethoxy)ethoxy]ethanol; TEGBE; triethylene glycol monobutyl ether - CAS: 143-22-6

a) acute toxicity:

Test: LD50 - Route: Dermal - Species: Rabbit = 3.54 ml/kg - Source: American Industrial Hygiene Association Journal. Vol. 23, Pg. 95, 1962.

Test: LD50 - Route: Oral - Species: Rat = 5300 mg/kg - Source: Office of Toxic Substances Report. Vol. OTS,

Triethanol amine - CAS: 102-71-6

a) acute toxicity:

Test: LD50 - Route: Oral - Species: Guinea pig = 2200 mg/kg - Source:

"Toxicometric Parameters of Industrial Toxic Chemicals Under Single Exposure," Izmerov, N.F., et al., Moscow, Centre of International Projects, GKNT, 1982Vol. -, Pg. 114, 1982.

Test: LD50 - Route: Oral - Species: Mouse = 5846 mg/kg - Source: Science Reports of the Research Institutes, Tohoku University, Series C: Medicine. Vol. 36(1-4), Pg. 10, 1989.

If not differently specified, the information required in Regulation (EU) 2015/830 listed below must be considered as 'No data available':

- a) acute toxicity;
- b) skin corrosion/irritation;
- c) serious eye damage/irritation;
- d) respiratory or skin sensitisation;
- e) germ cell mutagenicity;
- f) carcinogenicity;
- g) reproductive toxicity;

Safety Data Sheet

- h) STOT-single exposure;
- i) STOT-repeated exposure;
- j) aspiration hazard.

SECTION 12: Ecological information

- 12.1. Toxicity
Adopt good working practices, so that the product is not released into the environment.
No data available
- 12.2. Persistence and degradability
No data available
- 12.3. Bioaccumulative potential
No data available
- 12.4. Mobility in soil
No data available
- 12.5. Results of PBT and vPvB assessment
vPvB Substances: None - PBT Substances: None
- 12.6. Other adverse effects
None

SECTION 13: Disposal considerations

- 13.1. Waste treatment methods
Recover if possible. In so doing, comply with the local and national regulations currently in force.

SECTION 14: Transport information

- 14.1. UN number
Not classified as dangerous in the meaning of transport regulations.
- 14.2. UN proper shipping name
No data available
- 14.3. Transport hazard class(es)
No data available
- 14.4. Packing group
No data available
- 14.5. Environmental hazards
No data available
- 14.6. Special precautions for user
No data available
- 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code
No data available

SECTION 15: Regulatory information

- 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture
 - Dir. 98/24/EC (Risks related to chemical agents at work)
 - Dir. 2000/39/EC (Occupational exposure limit values)
 - Regulation (EC) n. 1907/2006 (REACH)
 - Regulation (EC) n. 1272/2008 (CLP)
 - Regulation (EC) n. 790/2009 (ATP 1 CLP) and (EU) n. 758/2013
 - Regulation (EU) 2015/830
 - Regulation (EU) n. 286/2011 (ATP 2 CLP)
 - Regulation (EU) n. 618/2012 (ATP 3 CLP)
 - Regulation (EU) n. 487/2013 (ATP 4 CLP)
 - Regulation (EU) n. 944/2013 (ATP 5 CLP)
 - Regulation (EU) n. 605/2014 (ATP 6 CLP)

Safety Data Sheet

Restrictions related to the product or the substances contained according to Annex XVII Regulation (EC) 1907/2006 (REACH) and subsequent modifications:

Restrictions related to the product:

No restriction.

Restrictions related to the substances contained:

No restriction.

Where applicable, refer to the following regulatory provisions :

Directive 2003/105/CE ('Activities linked to risks of serious accidents') and subsequent amendments.

Regulation (EC) nr 648/2004 (detergents).

1999/13/EC (VOC directive)

Provisions related to directives 82/501/EC(Seveso), 96/82/EC(Seveso II):

No data available

15.2. Chemical safety assessment

No

SECTION 16: Other information

Full text of phrases referred to in Section 3:

H318 Causes serious eye damage.

H412 Harmful to aquatic life with long lasting effects.

H302 Harmful if swallowed.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H400 Very toxic to aquatic life.

Hazard class and hazard category	Code	Description
Acute Tox. 4	3.1/4/Oral	Acute toxicity (oral), Category 4
Skin Irrit. 2	3.2/2	Skin irritation, Category 2
Eye Dam. 1	3.3/1	Serious eye damage, Category 1
Skin Sens. 1,1A,1B	3.4.2/1-1A-1B	Skin Sensitisation, Category 1,1A,1B
Aquatic Acute 1	4.1/A1	Acute aquatic hazard, category 1
Aquatic Chronic 3	4.1/C3	Chronic (long term) aquatic hazard, category 3

Paragraphs modified from the previous revision:

SECTION 1: Identification of the substance/mixture and of the company/undertaking

SECTION 3: Composition/information on ingredients

SECTION 8: Exposure controls/personal protection

SECTION 11: Toxicological information

This document was prepared by a competent person who has received appropriate training.

Main bibliographic sources:

ECDIN - Environmental Chemicals Data and Information Network - Joint Research Centre, Commission of the European Communities

SAX's DANGEROUS PROPERTIES OF INDUSTRIAL MATERIALS - Eight Edition - Van Nostrand Reinold

CCNL - Appendix 1

Ref. 1 ·IARC Monographs on the Evaluation Carcinogenic Risks to Humans (IARC:

International Agency for Research on Cancer)

·Journal of Occupational Health (JOH) (Japan Society of Occupational Health (JSOH))

·TLVs and BEIs (ACGIH: American Conference of Governmental Industrial Hygienists)

·IRIS Carcinogenic Assessment (IRIS: Integrated Risk Information System of US EPA)

Safety Data Sheet

- National Toxicology Program (NTP) Report on Carcinogens
 - Annex VI of REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006
 - MAK und BAT Werte Liste (DFG: German Research Foundation)
 - TRGS 905, Verzeichnis krebserzeugender, keimzell mutagener oder reproduktionstoxischer Stoffe (AGS: Committee on Hazardous Substances, Germany)
- Ref. 2
- Annex VI of REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006
 - TRGS 905, Verzeichnis krebserzeugender, keimzell mutagener oder reproduktionstoxischer Stoffe (AGS: Committee on Hazardous Substances, Germany)

The information contained herein is based on our state of knowledge at the above-specified date. It refers solely to the product indicated and constitutes no guarantee of particular quality.

It is the duty of the user to ensure that this information is appropriate and complete with respect to the specific use intended.

This Safety Data Sheet cancels and replaces any preceding release.

ADR:	European Agreement concerning the International Carriage of Dangerous Goods by Road.
CAS:	Chemical Abstracts Service (division of the American Chemical Society).
CLP:	Classification, Labeling, Packaging.
DNEL:	Derived No Effect Level.
EINECS:	European Inventory of Existing Commercial Chemical Substances.
GefStoffVO:	Ordinance on Hazardous Substances, Germany.
GHS:	Globally Harmonized System of Classification and Labeling of Chemicals.
IATA:	International Air Transport Association.
IATA-DGR:	Dangerous Goods Regulation by the "International Air Transport Association" (IATA).
ICAO:	International Civil Aviation Organization.
ICAO-TI:	Technical Instructions by the "International Civil Aviation Organization" (ICAO).
IMDG:	International Maritime Code for Dangerous Goods.
INCI:	International Nomenclature of Cosmetic Ingredients.
KSt:	Explosion coefficient.
LC50:	Lethal concentration, for 50 percent of test population.
LD50:	Lethal dose, for 50 percent of test population.
LTE:	Long-term exposure.
PNEC:	Predicted No Effect Concentration.
RID:	Regulation Concerning the International Transport of Dangerous Goods by Rail.
STE:	Short-term exposure.
STEL:	Short Term Exposure limit.
STOT:	Specific Target Organ Toxicity.
TLV:	Threshold Limiting Value.
TWATLV:	Threshold Limit Value for the Time Weighted Average 8 hour day. (ACGIH Standard).
WGK:	German Water Hazard Class.