

Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pluggable surge protective device, in accordance with Type 2/Class II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE). For systems with more stringent safety requirements.

The illustration shows version
VAL-SEC-T2-3S-350-FM

Your advantages

- ✓ Varistor arrester with a low leakage current
- ✓ High-performance gas-filled surge arrester for N/PE protection
- ✓ Extremely narrow design, just 12 mm per position
- ✓ Can be used in systems with more stringent safety requirements, thanks to the 40 kA discharge capacity
- ✓ High continuous voltage of 350 V AC for 230/400 V AC networks with high voltage fluctuations
- ✓ Pluggable
- ✓ Low voltage protection level of 1.5 kV
- ✓ Optical, mechanical status indicator
- ✓ Plugs can be checked with CHECKMASTER 2



Key commercial data

package_quantity	1
GTIN	4055626378220

Technical data

Dimensions

Height	89.9 mm
Width	49.2 mm
Depth	74.5 mm
Horizontal pitch	2.7 Div.

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m (amsl (above mean sea level))
Permissible humidity (operation)	5 % ... 95 %

Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Technical data

Ambient conditions

Shock (operation)	30g (half sinus / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

General

IEC test classification	II
IEC test classification	T2
EN type	T2
IEC power supply system	TN-S
IEC power supply system	TT
Mode of protection	L-N
Mode of protection	L-PE
Mode of protection	N-PE
Mounting type	DIN rail: 35 mm
Color	light grey RAL 7035
Color	traffic grey A RAL 7042
Housing material	PA 6.6-FR 20% GF
Housing material	PBT-FR
Degree of pollution	2
Flammability rating according to UL 94	V-0
Design	DIN rail module, two-section, divisible
Number of positions	4
Surge protection fault message	optical

Protective circuit

Nominal voltage U_N	240/415 V AC (TN-S)
Nominal voltage U_N	240/415 V AC (TT)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_c (L-N)	350 V AC
Maximum continuous operating voltage U_c (L-PE)	350 V AC
Maximum continuous voltage U_c (N-PE)	264 V AC
Rated load current I_L	40 A (Biconnect M4 fork-type cable lug 6 mm ²)
Rated load current I_L	63 A (TWIN ferrule 2 x 10 mm ²)
Residual current I_{PE}	≤ 1 µA
Nominal discharge current I_n (8/20) µs (L-N)	20 kA
Nominal discharge current I_n (8/20) µs (L-PE)	20 kA
Nominal discharge current I_n (8/20) µs (N-PE)	40 kA
Maximum discharge current I_{max} (8/20) µs (L-N)	40 kA
Maximum discharge current I_{max} (8/20) µs (L-PE)	40 kA
Maximum discharge current I_{max} (8/20) µs (N-PE)	80 kA
Follow current interrupt rating I_{fi} (N-PE)	100 A (264 V AC)
Short-circuit current rating I_{SCCR}	25 kA (in case of 315 A gG backup fuse)
Short-circuit current rating I_{SCCR}	50 kA (in case of 200 A gG backup fuse)

Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Technical data

Protective circuit

Voltage protection level U_p (L-N)	≤ 1.5 kV
Voltage protection level U_p (L-PE)	≤ 1.9 kV
Voltage protection level U_p (N-PE)	≤ 1.5 kV
Residual voltage U_{res} (L-N)	≤ 1.5 kV (at I_n)
Residual voltage U_{res} (L-N)	≤ 1.3 kV (at 10 kA)
Residual voltage U_{res} (L-N)	≤ 1.2 kV (at 5 kA)
Residual voltage U_{res} (L-N)	≤ 1.1 kV (at 4 kA)
Residual voltage U_{res} (L-N)	≤ 1 kV (at 2 kA)
Residual voltage U_{res} (N-PE)	≤ 0.7 kV (at I_n)
Residual voltage U_{res} (N-PE)	≤ 0.7 kV (at 20 kA)
Residual voltage U_{res} (N-PE)	≤ 0.7 kV (at 8 kA)
Residual voltage U_{res} (N-PE)	≤ 0.7 kV (at 4 kA)
TOV behavior at U_T (L-N)	415 V AC (5 s / withstand mode)
TOV behavior at U_T (L-N)	457 V AC (120 min / safe failure mode)
TOV behavior at U_T (N-PE)	1200 V AC (200 ms / withstand mode)
Response time t_A (L-N)	≤ 25 ns
Response time t_A (L-PE)	≤ 100 ns
Response time t_A (N-PE)	≤ 100 ns
Max. backup fuse with branch wiring	315 A (gG)
Max. backup fuse with V-type through wiring	40 A (gG / Biconnect M4 fork-type cable lug, 6 mm ²)
Max. backup fuse with V-type through wiring	63 A (gG / TWIN ferrule 2x 10mm ²)

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	4.5 Nm
Stripping length	16 mm
Conductor cross section flexible	2.5 mm ² ... 16 mm ²
Conductor cross section solid	2.5 mm ² ... 25 mm ²
Conductor cross section AWG	12 ... 4

Standards and Regulations

Standards/regulations	IEC 61643-11 2011
Standards/regulations	EN 61643-11 2012

Classifications

eCl@ss

eCl@ss 5.1	27130801
eCl@ss 6.0	27130805
eCl@ss 8.0	27130805
eCl@ss 9.0	27130805

Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Classifications

ETIM

ETIM 5.0	EC000941
ETIM 6.0	EC000941

Approvals

KEMA-KEUR / EAC /

Approval details

KEMA-KEUR 

EAC EAC

Accessories

End block

CLIPFIX 35 - 3022218



Marker pen

X-PEN 0,35 - 0811228



Device marking

EML (20XE)R - 0803452



Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Accessories

EML (20XE)R YE - 0803453



ZBN 18:UNBEDRUCKT - 2809128



ZBN 18:UNBEDRUCKT - 2809128



Labeled device marker

ZBN 18,LGS:L1-N,ERDE - 2749576



ZBN 18,LGS:ERDE - 2749589



Terminal marking

Type 2 surge arrester - VAL-SEC-T2-3S-350/40 - 2909637

Accessories

ZBFM 5/WH:UNBEDRUCKT - 0803595




Accessories

ZBN 18:SO/CMS - 0800763




Drawings

Dimensional drawing



Circuit diagram



Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>