



8	FERRULE	BRASS	1	NICKEL
7	CENTER PIN	PHOSPHOR BRONZE	1	GOLD
6	BODY	BRASS	1	NICKEL
5	BODY	BRASS	1	NICKEL
4	INSULATOR	TEFLON	1	
3	INNER RETAINING RING	STAINLESS	1	NICKEL
2	GASKET	S.L.RUBBER	1	
1	SHELL	BRASS	1	NICKEL
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

Dimensions Are In Millimeters

Unless Otherwise Specified

Tolerances

0.5-6 =  $\pm 0.2$

6-30 =  $\pm 0.4$

30-120 =  $\pm 0.6$

120-315 =  $\pm 1.0$

315-1000 =  $\pm 1.6$

1000-2000 =  $\pm 2.4$