


Unit = mm



Spring type vibration switch

Voltage:	<12V
Current:	<20mA
Conductive time:	About 2ms
Closed resistance:	<30 ohm
Open resistance:	>10M ohm
Temperature range:	-40 to 80°C
Pull force of terminal:	500gf for 1 minute
Humidity:	95% RH, 40°C for 96 hours
Operating lifespan:	Above 200000 circle

Features:

Switch is open circuit OFF-state at rest. when the external force is touched, or the speed of movement is appropriate, the switch transient ON-state, when external force disappear, switch back to open circuit OFF-state.

