

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Product form : Mixture  
Product name : 007361 - TROPICOAT  
UFI : GYCN-DOX8-R00X-DK5T  
Product code : 007361  
Type of product : Aerosol, Varnish  
Vaporizer : Aerosol

**1.2. Relevant identified uses of the substance or mixture and uses advised against****1.2.1. Relevant identified uses**

Main use category : Equipment polish  
Industrial/Professional use spec : Industrial  
For professional use only

**1.2.2. Uses advised against**

No additional information available

**1.3. Details of the supplier of the safety data sheet**

ITW Spraytec  
42, rue Gallieni  
F-92600 Asnières sur Seine - France  
T +33(0)1.40.80.32.32 - F +33(0)1.40.80.32.30  
[infofds@itwpc.com](mailto:infofds@itwpc.com) - [www.jelt.fr](http://www.jelt.fr)

**1.4. Emergency telephone number**

Emergency number : FRANCE :+ 33 (0)1 45 42 59 59

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Newcastle Centre) Regional Drugs and Therapeutics Centre, Wolfson Unit	Claremont Place Newcastle-upon-Tyne NE1 4LP Newcastle	0344 892 0111	

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Aerosol, Category 1 H222;H229  
Serious eye damage/eye irritation, Category 2 H319  
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336  
Full text of H statements : see section 16

**Adverse physicochemical, human health and environmental effects**

No additional information available

**2.2. Label elements****Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP) :



# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

	GHS02	GHS07
Signal word (CLP)	: Danger	
Contains	: ethyl acetate	
Hazard statements (CLP)	: H222 - Extremely flammable aerosol. H229 - Pressurised container: May burst if heated. H319 - Causes serious eye irritation. H336 - May cause drowsiness or dizziness.	
Precautionary statements (CLP)	: P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 - Do not spray on an open flame or other ignition source. P251 - Do not pierce or burn, even after use. P261 - Avoid breathing dust/fume/gas/mist/vapours/spray. P271 - Use only outdoors or in a well-ventilated area. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. P102 - Keep out of reach of children.	
EUH-statements	: EUH066 - Repeated exposure may cause skin dryness or cracking.	

### 2.3. Other hazards

No additional information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ethyl acetate	(CAS-No.) 141-78-6 (EC-No.) 205-500-4 (EC Index-No.) 607-022-00-5 (REACH-no) 01-2119475103-46	30 – 50	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
butane	(CAS-No.) 106-97-8 (EC-No.) 203-448-7	10 – 30	Flam. Gas 1A, H220 Press. Gas (Liq.), H280
n-butyl acetate	(CAS-No.) 123-86-4 (EC-No.) 204-658-1 (EC Index-No.) 607-025-00-1 (REACH-no) 01-2119485493-29	< 20	Flam. Liq. 3, H226 STOT SE 3, H336
Propane	(CAS-No.) 74-98-6 (EC-No.) 200-827-9 (REACH-no) 01-2119486944-21	< 10	Flam. Gas 1A, H220 Press. Gas (Liq.), H280
2,5 thiophenediylbis(5-tert-butyl-1,3-benzoxazole)	(CAS-No.) 7128-64-5	≤ 0,1	Aquatic Chronic 4, H413

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general	: Call a POISON CENTER/doctor/physician if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

First-aid measures after ingestion : Call a POISON CENTER/doctor/physician if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : May cause drowsiness or dizziness.  
Symptoms/effects after eye contact : Eye irritation.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Water haze. Carbon dioxide. Foam.  
Unsuitable extinguishing media : Do not use a heavy water stream.

### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Extremely flammable aerosol.  
Explosion hazard : Pressurised container: May burst if heated.  
Hazardous decomposition products in case of fire : Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

### 5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

No additional information available

#### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Mechanically recover the product.  
Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Use only outdoors or in a well-ventilated area. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes. Wear personal protective equipment.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.
Incompatible materials	: Sources of ignition. Direct sunlight. Heat sources.
Storage temperature	: < 50 °C

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

ethyl acetate (141-78-6)	
<b>France - Occupational Exposure Limits</b>	
Local name	Acétate d'éthyle
VME (mg/m <sup>3</sup> )	1400 mg/m <sup>3</sup>
VME (ppm)	400 ppm
<b>Germany - Occupational Exposure Limits (TRGS 900)</b>	
TRGS 900 Local name	Ethylacetat
TRGS 900 Occupational exposure limit value (mg/m <sup>3</sup> )	1500 mg/m <sup>3</sup>
TRGS 900 Occupational exposure limit value (ppm)	400 ppm
TRGS 900 Limitation of exposure peaks (mg/m <sup>3</sup> )	3000 mg/m <sup>3</sup>
TRGS 900 Limitation of exposure peaks (ppm)	800 ppm
<b>United Kingdom - Occupational Exposure Limits</b>	
Local name	Ethyl acetate
WEL TWA (ppm)	200 ppm
WEL STEL (ppm)	400 ppm

butane (106-97-8)	
<b>France - Occupational Exposure Limits</b>	
Local name	n-Butane
VME (mg/m <sup>3</sup> )	1900 mg/m <sup>3</sup>
VME (ppm)	800 ppm
<b>United Kingdom - Occupational Exposure Limits</b>	
Local name	Butane
WEL TWA (mg/m <sup>3</sup> )	1450 mg/m <sup>3</sup>
WEL TWA (ppm)	600 ppm
WEL STEL (mg/m <sup>3</sup> )	1810 mg/m <sup>3</sup>
WEL STEL (ppm)	750 ppm
Remark (WEL)	Carc. (only applies if Butane contains more than 0.1% of buta-1,3-diene)

n-butyl acetate (123-86-4)	
<b>France - Occupational Exposure Limits</b>	
Local name	Acétate de n-butyle

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

n-butyl acetate (123-86-4)	
VME (mg/m <sup>3</sup> )	710 mg/m <sup>3</sup>
VME (ppm)	150 ppm
VLE (mg/m <sup>3</sup> )	940 mg/m <sup>3</sup>
VLE (ppm)	200 ppm
Germany - Occupational Exposure Limits (TRGS 900)	
TRGS 900 Local name	n-Butylacetat
TRGS 900 Occupational exposure limit value (mg/m <sup>3</sup> )	300 mg/m <sup>3</sup>
TRGS 900 Occupational exposure limit value (ppm)	62 ppm
TRGS 900 Limitation of exposure peaks (mg/m <sup>3</sup> )	600 mg/m <sup>3</sup>
TRGS 900 Limitation of exposure peaks (ppm)	124 ppm
United Kingdom - Occupational Exposure Limits	
Local name	Butyl acetate
WEL TWA (mg/m <sup>3</sup> )	724 mg/m <sup>3</sup>
WEL TWA (ppm)	150 ppm
WEL STEL (mg/m <sup>3</sup> )	966 mg/m <sup>3</sup>
WEL STEL (ppm)	200 ppm

## 8.2. Exposure controls

### Appropriate engineering controls:

Ensure good ventilation of the work station.

### Materials for protective clothing:

Wear suitable protective clothing

### Hand protection:

In case of repeated or prolonged contact wear gloves. Chemical resistant gloves (according to European standard NF EN 374 or equivalent). The choice of appropriate gloves depends not only on the material, but also on other quality criteria that may vary from one manufacturer to another. As the product is a preparation made from several substances, glove material resistance may not be calculated in advance and must be tested before use. The exact penetration time of glove material is to be determined by the manufacturer of protective gloves and respected.

### Eye protection:

Safety glasses

### Skin and body protection:

Wear suitable protective clothing

### Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

### Personal protective equipment symbol(s):



# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### Environmental exposure controls:

Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Organic solvent.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: < 0 °C
Flash point	: < 0 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: 0,914 g/cm <sup>3</sup>
Solubility	: insoluble in water. soluble in most organic solvents.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: Pressurised container: May burst if heated.
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Extremely flammable aerosol. Pressurised container: May burst if heated.

### 10.2. Chemical stability

Stable under normal conditions. Extremely flammable aerosol. Heating may cause a fire or explosion.

### 10.3. Possibility of hazardous reactions

None under normal conditions.

### 10.4. Conditions to avoid

Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified

##### ethyl acetate (141-78-6)

LD50 oral rat	> 2000 mg/kg
LD50 dermal rabbit	> 2000 mg/kg

##### n-butyl acetate (123-86-4)

LD50 oral rat	10760 mg/kg
LD50 dermal rabbit	> 14112 mg/kg
LC50 inhalation rat (mg/l)	23,4 mg/l/4h

Skin corrosion/irritation : Not classified  
Serious eye damage/irritation : Causes serious eye irritation.  
Respiratory or skin sensitisation : Not classified  
Germ cell mutagenicity : Not classified  
Carcinogenicity : Not classified

Reproductive toxicity : Not classified

STOT-single exposure : May cause drowsiness or dizziness.

STOT-repeated exposure : Not classified

Aspiration hazard : Not classified

#### 007361 - TROPICOAT

Vaporizer	Aerosol
-----------	---------

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.  
Hazardous to the aquatic environment, short-term (acute) : Not classified  
Hazardous to the aquatic environment, long-term (chronic) : Not classified

##### ethyl acetate (141-78-6)

LC50 fish 1	> 100 mg/l
EC50 other aquatic organisms 1	> 100 mg/l
ErC50 (algae)	> 100 mg/l

##### n-butyl acetate (123-86-4)

LC50 fish 1	18 mg/l
EC50 Daphnia 1	44 mg/l

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ErC50 (algae)	647,7 mg/l
NOEC chronic algae	200 mg/l

### 12.2. Persistence and degradability

<b>ethyl acetate (141-78-6)</b>	
Biodegradation	> 70 % OCDE 301 D 28 days

### 12.3. Bioaccumulative potential

<b>ethyl acetate (141-78-6)</b>	
Partition coefficient n-octanol/water (Log Pow)	0,68

<b>n-butyl acetate (123-86-4)</b>	
Partition coefficient n-octanol/water (Log Kow)	2,3

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

No additional information available




## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Product/Packaging disposal recommendations : Container under pressure. Do not drill or burn even after use. Dispose in a safe manner in accordance with local/national regulations.

## SECTION 14: Transport information

In accordance with ADR / IATA / IMDG

ADR	IMDG	IATA
<b>14.1. UN number</b>		
UN 1950	UN 1950	UN 1950
<b>14.2. UN proper shipping name</b>		
AEROSOLS	AEROSOLS	Aerosols, flammable
<b>Transport document description</b>		
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1
<b>14.3. Transport hazard class(es)</b>		
2.1	2.1	2.1
		



# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 14.4. Packing group

Not applicable

Not applicable

Not applicable

### 14.5. Environmental hazards

Dangerous for the environment : No

Dangerous for the environment : No  
Marine pollutant : No

Dangerous for the environment : No

No supplementary information available

### 14.6. Special precautions for user

#### Overland transport

Classification code (ADR) : 5F  
Special provisions (ADR) : 190, 327, 344, 625  
Limited quantities (ADR) : 1I  
Excepted quantities (ADR) : E0  
Packing instructions (ADR) : P207  
Special packing provisions (ADR) : PP87, RR6, L2  
Mixed packing provisions (ADR) : MP9  
Transport category (ADR) : 2  
Special provisions for carriage - Packages (ADR) : V14  
Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12  
Special provisions for carriage - Operation (ADR) : S2  
Tunnel restriction code (ADR) : D

#### Transport by sea

Special provisions (IMDG) : 63, 190, 277, 327, 344, 381, 959  
Packing instructions (IMDG) : P207, LP200  
Special packing provisions (IMDG) : PP87, L2  
EmS-No. (Fire) : F-D  
EmS-No. (Spillage) : S-U  
Stowage category (IMDG) : None  
Stowage and handling (IMDG) : SW1, SW22  
Segregation (IMDG) : SG69  
MFAg-No : 126

#### Air transport

PCA Excepted quantities (IATA) : E0  
PCA Limited quantities (IATA) : Y203  
PCA limited quantity max net quantity (IATA) : 30kgG  
PCA packing instructions (IATA) : 203  
PCA max net quantity (IATA) : 75kg  
CAO packing instructions (IATA) : 203  
CAO max net quantity (IATA) : 150kg  
Special provisions (IATA) : A145, A167, A802  
ERG code (IATA) : 10L

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

### 15.1.2. National regulations

#### France

Occupational diseases : RG 84 - Affections engendrées par les solvants organiques liquides à usage professionnel

#### Germany

Water hazard class (WGK) : WGK 1, Slightly hazardous to water (Classification according to AwSV, Annex 1)

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

#### Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Borstvoeding

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Vruchtbaarheid

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Ontwikkeling

#### Denmark

Class for fire hazard : Class I-1

Store unit : 1 liter

Classification remarks : F+ <Aerosol 1>; Emergency management guidelines for the storage of flammable liquids must be followed

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product

### 15.2. Chemical safety assessment

No additional information available

## SECTION 16: Other information

Full text of H- and EUH-statements:	
Aquatic Chronic 4	Hazardous to the aquatic environment — Chronic Hazard, Category 4
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1A	Flammable gases, Category 1A
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Press. Gas (Liq.)	Gases under pressure : Liquefied gas
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H413	May cause long lasting harmful effects to aquatic life.
EUH066	Repeated exposure may cause skin dryness or cracking.

SDS EU (REACH Annex II)

# 007361 - TROPICOAT

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

---

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.