


Datenblatt

Impedance	50 Ω
Frequency range	0-5 GHz
Voltage rating	1500 volts peak
Dielectric withstanding voltage	2500 volts rms
VSWR	M39012 straight connectors: 1.3 max. 0-11GHz M39012 right angle: 1.35 max. 0-11GHz
othr (MIL-C-39012 cable connectors)	Contact resistance: center contact 1.0 milliohm outer contact 0.2 milliohm Insertion loss: 0.15db max at 10.0GHz Insulation resistance: 5000 megohms(min)
Coupling Torque	15.0 lb-in (1.70 N.m)

3	Insulator	Delrin	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish



- NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER FIS-C3604
 2. CONNECTOR INTERFACE PER MIL-STD-348A
 3. PART TO BE CLEAN AND FREE BURRS
 4. NICKEL PL TO 0" THICK OVER COPPER STRIKE
 5. GOLD PL 1-3 0" OVER NICKEL PL TO 0" THICK OVER COPPER STRIKE