

ELECTRICAL CHARACTERISTIC		
(1)	INNER CONTACT RESISTANCE:<math>< 10\text{m}\Omega</math>	
(2)	OUTER CONTACT RESISTANCE:<math>< 2.5\text{m}\Omega</math>	
(3)	WITHSTAND VOLTAGE:DC1500V	
(4)	CURRENT RATING:3A/DC1500V	
(5)	OPERATING TEMPERATURE:$-30/+60^{\circ}\text{C}$	
6	SCREW	BRASS
5	DIELECTRIC	POM
4	BODY	BRASS
3	SHELL	BRASS
2	FERRULE	BRASS
1	PIN	BRASS
ITEM	DESIGNATION	MATERIAL

