

EBR 2

Description:

- Filling and emptying control of two elements (well and tank) with a single device.
- Adjustable sensitivity depending on water conductivity.
- Reinforced protection against lightning.
- Allows for monitoring the filling of a deposit or a tank from a well.
- Modular format for installation on DIN rail, four modules wide (70 mm.).
- Enhanced protection against storm disruptions through varistors in the power input and the probes.
- Front potentiometer to adjust probe sensitivity.
- LED indicator of relay status.
- Dual voltage power supply at 230 V a.c. or 400 V a.c.
- Accessories: Needs two kits of 3 probes (2 x ref. OB230300).



Technical specifications:

- Power supply: 230 or 400 Va.c., 50-60 Hz.
- Switching capacity: 8 (2) A 250 Va.c., 4 (1) A 400 Va.c.
- Probe voltage: 13 Va.c.
- Adjustable sensitivity: from 0 kO to 50 kO
- Operating temp.: -10 °C to +45 °C according to EN 60730-2-7
- Protection degree: IP 20 according to EN 60529

