



RECOMMENDED P.C.B. PATTERN LAYOUT
TOP VIEW (TOLERANCE: ±0,05)



1. Material:

Contacts :Brass

Insulator:PBT+30%G.F UL94V-0

Shell : Brass

2. Mechanical:

Mating Force:45N max.

Withdrawal Force:7N min.

Durability:500 cycles min.

3. Electrical:

Current-max[amps] 1.0A

Voltage-max[volts] 30V

Withstanding Voltage 750V AC

Contact Resistance [ohms] 30 milliohms max

Insulation Resistance [ohms] 1000 Megohms min

4. Plating:

Contacts: Gold Flash Selective over Nickel

Shell:Nickel

5. Environmental

Temperature Range -55°C~+85°C

RoHS compliant

Unit: mm