


















Male

Female



Recommended Panel Cut-Out

POSITION	A	B	C	D
15	24.99	20.47	10.67	12.01



P.C.B LAYOUT PATTERN

Product Specification

Material
 Insulator :Glass-Filled Thermoplastic PBT,UL94V-0 rated ,Black
 Contact :Copper alloy, Gold flash full gold
 Shell : Steel,100u" Tin Over 50u" min Copper
 Clinch Nut: Brass, 100u" min Nickel Plated
 Boardlock :Brass, 100u" min Nickel Plated.
 Screwlock :Brass, 100u" min Nickel Plated.

Electrical
 Contact Resistance :20 milliohms Max at 1 AMP DC.
 Insulation Resistance :1000 megohms at 500 VDC
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
 Current Rating :3 AMP
 Volatge Rating :250 VAC/rms 60Hz
 Operating Temperature: -55°C ~ +105°C

Dimensions	Positions	A	B	C	E
	15	30.81	24.99	16.92	2.29

Product Specification

Material
 Insulator :Glass-Filled Thermoplastic PBT,UL94V-0 rated ,Black
 Contact :Copper alloy, Gold flash full gold
 Shell : Steel,100u" Tin Over 50u" min Copper
 Clinch Nut: Brass, 100u" min Nickel Plated
 Boardlock :Brass, 100u" min Nickel Plated.
 Screwlock :Brass, 100u" min Nickel Plated.

Electrical
 Contact Resistance :20 milliohms Max at 1 AMP DC.
 Insulation Resistance :1000 megohms at 500 VDC
 Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
 Current Rating :3 AMP
 Volatge Rating :250 VAC/rms 60Hz
 OPERATING TEMPERATURE:-55°C+105°C

Dimensions	Positions	A	B	D	E
	15	30.81	24.99	16.33	2.29

Positions	G	H
15M/F	1.145	7.04

Positions	G	H
15MF	1.145	7.04