

# GE**OHM** 5 Earth Tester

3-349-417-03 6/10.15

Battery operated earth tester per DIN VDE 0413, part 5, for measuring earth resistance. This instrument can also be used to ascertain or measure soil resistivity and ohmic resistance in accordance with the current-voltage measuring method.

- Measurement of:
  - Earth resistance
  - Selective earth resistance
  - Soil resistivity
  - Current (TRMS) via current clamp transformer (optional)
- Three or four-pole measuring method
- No balancing required
- Continuous monitoring of interference voltage and auxiliary earth electrode resistance with indication if allowable limit values are violated
- Data storage for 250 measurements (1000 measured values)
- Data interface for transmission of measured values to a PC
- Software (optional accessory) for measured value storage and report generation at a PC (in preparation)



# **Application**

This instrument offers three different ways of measuring earth resistance, as well as measurement of soil resistivity and current. The current clamp transformers which are required for certain measurements are available as optional accessories.

Measurable Quantities	Switch Position	Required Accessory
Earth resistance RE (traditional 4-wire method according to Wenner)	R <sub>EARTH</sub>	4 earth spikes and 4 measurement cables (included)
Selective earth resistance RS (traditional 4-wire method with additional current clamp transformers)	R <sub>S</sub> (clip)	4 earth spikes, 4 measure- ment cables, 1 current clamp transformer (optional)
Earth resistance RE (two current clamp transformers) – actually, loop resistance is measured!	R <sub>E</sub> (two current clamp transformers)	2 current clamp transformers (optional)
Soil resistivity	PEARTH	4 earth spikes and 4 meas- urement cables (included)
Current (TRMS)	I <sub>CLAMP</sub>	1 current clamp transformer (optional)



# **Applicable Regulations and Standards**

IEC 61 010-1/EN 61 010-1/ VDE 0411-1	Safety requirements for electrical equipment for measurement, control and laboratory use — General requirements	
IEC 61557/ EN 61557/ VDE 0413	Devices for testing, measuring or monitoring protective measures Part 1: General requirements Part 5: Earth resistance	
EN 60529 VDE 0470, part 1	Test instruments and test procedures Degrees of protection provided by enclosures (IP code)	
DIN EN 61326 VDE 0843, part 20	Electrical equipment for control technology and laboratory use – EMC requirements	

# Regulations and Standards for Use of the Test Instrument

-		
DIN VDE 0413, part 5	Devices for testing, measuring or monitoring protective measures; earth resistance  Stipulations for the setup of electric power installations with nominal voltages of up to 1000 V	
DIN VDE 0100		
DIN VDE 0141	Grounding in AC systems with nominal voltages of greater than 1 kV	
DIN VDE 0800	Setup and operation of telecommunications systems including data processing equipment; equipotential bonding and grounding	
DIN VDE 0185 Lightning protection systems – general setup		
International regulations and standards		
BS 7430 + BS 7671, NFC 15-100, IEC 60364		

# GEOHM 5 Earth Tester

## **Technical Data**

Function (per EN 61557)	GE <b>OHM</b> 5
Measuring voltage	40 V
Measuring frequency	125/150 Hz
Rs	Max. 50 kΩ
Rh	Max. 50 kΩ
3-pole measurement	
Measuring range	0.11 $\Omega$ to 19.99 k $\Omega$
Resolution	0.01 $\Omega$ to 10 $\Omega$
Measuring error	± (2% rdg. + 3d)
4-pole measurement	
Measuring range	0.11 $\Omega$ to 19.99 k $\Omega$
Resolution	0.01 $\Omega$ to 10 $\Omega$
Measuring Error	± (2% rdg. + 3d)
3-pole selective measurement with current clamp transfor	
Measuring range	0.11 $\Omega$ to 1.99 k $\Omega$
Resolution	0.01 $\Omega$ to 10 $\Omega$
Measuring error	± (2% rdg. + 3d)
4-pole selective measurement with current clamp transfor	
Measuring range	$0.00~\Omega$ to $1.99~k\Omega$
Resolution	0.01 $\Omega$ to 10 $\Omega$
Measuring error	± (2% rdg. + 3d)
2-clip measuring method	
Measuring range	$0.0~\Omega$ to $100~\Omega$
Resolution	0.1 $\Omega$ to 1 $\Omega$
Measuring error	±(10% rdg. + 2d)

Key: d = digit(s), rdg. = reading (measured value)

# Earth Resistance, 3/4-Pole Method

Measuring range RE (0.11 to 19.99  $k\Omega$ )

Display range ( $\Omega$ )	Resolution ( $\Omega$ )	Measuring error
0.00 to 19.99	0.01	
20.0 to 199.9	0.1	(20/ rdg + 2 digita)
200 to 999	1	(2% rdg. + 3 digits)
1.000 k to 1.999 k	1	
2.00 k to 19.99 k	10	(5% rdg.)

Additional error caused by the spike at Rc max. or Rp max.	$\pm$ (3% rdg. + 10 digits)
Rc max. <sup>1)</sup>	The smaller value of (4 k $\Omega$ +100·RE) or 50 k $\Omega$
Rp max. <sup>1)</sup>	The smaller value of (4 k $\Omega$ +100·RE) or 50 k $\Omega$
Additional error caused by 3 V interference voltage (50 Hz)	(5% rdg. + 10 digits)
Test voltage at the test sockets	40 V AC
Type of test voltage	Sine
Test voltage frequency	125 (countries with 50 Hz) / 150 (countries with 60 Hz)
Short-circuit test current	< 20 mA
Automatic resistance test at current and potential spikes	Yes
Automatic interference voltage test	Yes

 $<sup>^{1)}</sup>$  R<sub>C</sub> = R<sub>H</sub> (Hilfserder); R<sub>P</sub> = R<sub>S</sub> (Sonde)

## Earth Resistance with current clamp transformer and 4-Pole Test Method

The technical data are the same as for the 4-pole method except for display range and measuring range (see deviating values below).

#### Measuring Ranges RE (0.11 to 1.99 k $\Omega$ )

Display Range (Ω)	Resolution ( $\Omega$ )	Measuring Error
0.00 to 19.99	0.01	
20.0 to 199.9	0.1	(2% rdg. + 3 digits)
200 to 999	1	(2% rug. + 3 uigits)
1.00 k to 1.99 k	10	

## Additional Specifications

A Control Cont		
Additional error for interference voltage, indicated by displaying the interference voltage warning symbol (valid for maximum ratio $R_{earth\_total}$ / $RS=\frac{1}{2}$ )	(10% rdg. + 10 digits)	
Symbol for current noise	As of approx. 2.1 A	
Additional resistance ratio error	RS / R <sub>earth_total</sub> · 1%	
Display in case of too little current at the clip	Less than 0.5 mA	
Automatic interference voltage test	Yes	
Observe additional error caused by the clip.		

## Earth Resistance with 2 current clamp transformer

Display Range (Ω)	Resolution ( $\Omega$ )	Measuring Error
0. 0 to 19.9	0.1	(2% rdg. + 10 digits)
20 . to 100	1	(20% rdg.)

<sup>\*</sup> Distance between current clamp transformer > 30 cm

Additional error at most insignificant interference voltage with warning symbol	(10% rdg. + 10 digits)
The symbol appears as of	I <sub>Rausch</sub> / I <sub>Signal</sub> > 100
Additional error caused by use of current clamp transformers must be taken into consideration.	

#### Soil Resistivity

All of the technical data for the 4-pole method apply here too, except for display range (see deviations listed below).

Display Range (Ωm)	Resolution (Ωm)	Measuring Error
0.00 to 19.99	0.01	See measuring error for
20.0 to 199.9	0.1	RE measurement
200 to 1999	1	$\rho = 2\pi \text{ a-RE}$
2.00 K to 19.99 k	10	
20.0 k to 199.9 k	0.1 k	
200 k to 999 k (at 8 m)	- 1 k	(5% rdg.)
200 k to 1999 k (at 8 m)	I K	

Distance between the spikes is 1 to 30 m or 3 to 90 feet

GMC-I Messtechnik GmbH

## Current (TRMS AC) by means of current clamp transformer 1000:1 (optional accessories)

Display Range I (A)	Resolution (A)	Measuring Error
0 mA to 99.9 mA	0.1 mA	(5% rdg. + 3 digits)
100 mA to 999 mA	1 mA	
1.00 A to 9.99 A	0.01 A	(5% rdg.)
10.0 A to 19.9 A	0.1 A	

Input impedance	10 Ω	
Transformation ratio	1 A / 1 mA	
Nominal frequency	50 / 60 Hz	
Additional error caused by the current clamp transformers must be taken into consideration.		

#### **Reference Conditions**

Battery voltage  $5.5 V \pm 1\%$ +23 °C ± 2 K Ambient temperature Relative humidity 40 to 60%

#### **Electromagnetic Compatibility (EMC)**

Interference emission/

IEC 61326/EN 61326 immunity

#### **Ambient Conditions**

10 to +30 °C Reference temp. range Operating temp. range 0 to + 40 °C

Relative humidity Max. 80% (at 0 to +40 °C) no condensation allowed

### **Power Supply**

**Batteries** 4 ea. 1.5 V baby cell (4 ea. C size) (alkaline manganese per IEC LR14)

4.8 V (4 ea. 1.2 V NiCd, NiMH Rechargeable batteries rechargeable batteries per IEC LR14)

Charger Upon request

Charging voltage

Due to lower charging capacity, fewer measurements are possible with rechargeable batteries than with normal batteries as a rule.

Battery saver circuit The test instrument is switched off

automatically approximately 10 minutes after the last key operation.

## **Electrical Safety**

Safety class Double insulated

#### **Mechanical Design**

Display Multiple display with LCD (61 x 33 mm)



Dimensions  $\times$  H  $\times$  D: 15.5  $\times$  9.5  $\times$  19 cm Weight Approx. 1.3 kg with batteries Protection Housing: IP 54 per EN 60529 Table Excerpt Regarding Significance of IP Codes

Table Execupt Hegalaning eighneance of it eedec					
IP XY (1 <sup>st</sup> char. X)	Protection against pene- tration by solid particles	IP XY (2 <sup>nd</sup> char. Y)	Protection against penetration by water		
5	Dust protected	4	Splashing water		

## **Data Interface**

RS 232C, serial, per DIN 19241 Type Format 9600 baud, no parity, 8 data bits,

1 stop bit

Connection 9-pin subminiature socket connector

# **Scope of Delivery**

- Earth tester
- Case (rugged, lockable Aluminium case)
- Neck strap
- Set batteries
- Earth spikes 4
- Measurement cables:

2 x 4 m, 1 x 15 m and 1 x 20 m

- Set operating instructions
- Proprietary calibration certificate





GMC-I Messtechnik GmbH

# GEOHM 5 Earth Tester

### **Accessories**

#### E-Clip 1 Current clamp transformer

Measuring range: 1 mA to 1200 A Measuring category: 600 V CAT III Max. cable diameter: 52 mm Transformation ratio: 1000 A/1A Frequency range: 40 Hz to 5 kHz Output signal: 1  $\mu$ A to 1.2 A

Supplied with connector cable (1.5 m) and laboratory safety plug



#### E-Clip 2 Current clamp transformer

Measuring range: 0.2 A to 1200 A
Measuring category: 600 V CAT III
Max. cable diameter: 52 mm
Transformation ratio: 1000 A/1A
Frequency range: 40 Hz to 5 kHz
Output signal: 0.2 mA to 1.2 A
Equipped with 4 mm safety sockets

Supplied with 2 test leads (red, black), each with stackable 4 mm safety plugs at both ends, approc. 1,5 m long



#### Charger

Input: 230 V AC, 50 Hz Output: 4.8 V DC, 350 mA Battery charging is indicated by means of a charging display.



## **Order Information**

Description	Туре	Article Number			
Earth tester set, see page 3	GEOHM   5	M591B			
Accessories	Accessories				
Charger with 4 NiMH rechargeable batteries	Z591C	Z591C			
Current clamp transformer Transformation ratio: 1000 A/1A Current measuring range: 1 mA to 1200 A Output signal: 1 µA to 1.2 A	E-Clip 1	Z591A			
Current clamp transformer Transformation ratio: 1000 A/1A Current meas. range: 0.2 A to 1200 A Output signal: 0.2 mA to 1.2 A	E-Clip 2	Z591B			
Earth tester set: Artificial leather pouch with 2 reels, 2 measurement cables (25 m ea.), 1 measurement cable (40 m), 2 measure- ment cables (3 m ea.), 4 earth spikes (zinc plated), 2 spike pullers, 1 hammer	E-Set 3	GTZ3301005R0001			
Earth tester set: Artificial leather pouch with two reels, 2 measurement cables (25 m ea.), 1 measurement cable (40 m), 2 meas- urement cables (3 m ea.), 4 earth drills	E-Set 4	Z590A			
Reel with 25 m measurement cable and banana plugs on the ends	TR25	GTZ3303000R0001			
Drum with 50 m measurement cable, banana plug and socket	TR50	GTY1040014E34			
Earth drill, 35 cm long, connection option for 4 mm banana plug	SP350	GTZ3304000R0001			

For additional information regarding accessories please refer to

- The data sheet for the respective device or our Measuring Instruments and Testers catalogue.
- www.gossenmetrawatt.com

 $\label{eq:power_power_power} \textbf{Prepared in Germany} \bullet \textbf{Subject to change without notice} \bullet \textbf{PDF version available on the Internet}$ 

