





## Starter Button Switch (printing 10A24VDC)

Rating	10A 24V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST OFF-(ON)		
Operation Force	750±150gf		

Material:  
Housing: ABS, Black  
Button: ABS, Black  
Terminal: Nickel plated brass



Unit: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.3

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.