

# PROFITEST H+E TECH Communication Tester Between Electric Charging Station and Vehicle

3-349-877-03 1/4.16

- Complete diagnosis of electric charging stations and vehicles with a single test instrument:
  - Vehicle states
  - Cable condition
  - Error states
  - PWM signal evaluation
  - Phases and phase sequence
  - Battery level
- An electric vehicle can be simulated in order to diagnose a charging station
- Indication of states by means of easy-to-understand symbols
- Easy operation and diagnostics (for persons with basic electro-technical instruction as well)
- Compact, battery powered device which is thus suitable for outdoor use
- Displays communication between the charging station and the electric vehicle in real-time



## **Applications**

The test instrument is intended for examining the functional performance of charging stations for electric vehicles with type 2 connector socket (mode 3 charging).

The test instrument is connected between the charging station and the electric vehicle to this end, in order to document communication between the two. If the charging process doesn't start, the source of error (charging station or electric vehicle) can be quickly pinpointed.

The range of applications includes R&D and service.

#### Features

- Connection option for electric vehicles: type II OEM plug
- Compact case, ideal for service calls
- Large display, for which background illumination can be activated
- Selectable user interface language the following languages are available: D, GB, F, E, I, P
- Power supply via two 9 V (rechargeable) block batteries or power pack
- USB data interface for firmware updates

#### Battery Charging Status – Power Saving Circuit

The battery charging status is indicated by means of 6 progressive segments.

The device is switched off automatically if none of the rotary switches are activated for a period of 10 minutes. Display illumination is deactivated automatically after 30 seconds.

#### **Diagnostics Information**

Measuring Parameter	Setting
Phase L1, L2, L3	On/off
Phase sequence	CW / CCW
Resultant charging current (via evaluation of the duty cycle)	A
PWM signal	
Frequency	Hz (set = 1 kHz)
Duty cycle (with PWM)	%
Upper voltage	3, 6, 9, 12 V
Lower voltage	– 12 V

#### **Status Visualization**

Displayable Vehicle Statuses (CP)	
No vehicle connected	•
Vehicle connected	•
Vehicle ready for charging without ventilation	•
Vehicle ready for charging with ventilation	•
Cable Type (PP)	
No cable	—
13 A cable	—
20 A cable	•
32 A cable	—
63 A cable	—

# PROFITEST H+E TECH Communication Tester Between Electric Charging Station and Vehicle

# **Technical Data**

Input voltage	400 V (3-phase)
Frequency	50 Hz
Test consumer power	max. 2.9 kVA

### **Electrical Safety**

Protection class Nominal voltage Test voltage Measuring category Pollution degree Fuses

I 400 V DC 500 V DC CAT III, 300 V 2 None

## Mechanical Design

Dimensions Weight Protection

W x L x H = 200 x 240 x 115 mm
3.65 kg
IP 21

## Display

<sup>L1</sup> ☆ <sup>L2</sup> ☆ <sup>L</sup>	<sup>3</sup> ∰ <sup>R</sup> Č	
evaluation of <u>pwm</u>	signal	
<u>voltage</u> positive	0,0V	
<u>voltage</u> negative	0,0V	
<u>pwm frequency</u>	<u>no signal</u>	
<u>charging</u> current	0 A	
<u>duty dycle</u> :	0%	
<u>Switch-off</u> time:	1mS	
	≫→₽	
Display	Multiple display with do	t matrix,

240 x 128 pixels, diagonal: 10.7 cm (4.2")

Abbreviations and Their Meanings

ADDIEVIAUOIIS AITU TITEII MEATIITYS		
Symbol	Meaning	
CP	Displayable vehicle statuses	
PP	Cable type	
CP-PE	Resistance coding for enabling charging	
PP-PE	Resistance coding for maximum charging current relative to conductor cross-section or cable type	
PWM signal	Pulse-width modulated signal for communication with the vehicle via the CP cable	
RCD	Residual current circuit breaker	

### **Ambient Conditions**

Operating temperature- 10 °C ... +45 °CStorage temperature- 25 °C ... +60 °CRelative humiditymax. 80%, condensation is ruled out

## **Applicable Regulations and Standards**

IEC 61010-1/EN 61010-1/ VDE 0411-1	Safety requirements for electrical equipment for mea- surement, control and laboratory use – General requirements
IEC 61851-1	Electric vehicle conductive charging system
DIN EN 61851-1	– Part 1: General requirements
DIN EN 61326-1 VDE 0843-20-1	Electrical equipment for measurement, control and lab- oratory use – EMC requirements – Part 1: General re- quirements
EN 60529	Test instruments and test procedures
VDE 0470-1	Degrees of protection provided by enclosures (IP code)

## **Scope of Delivery**

- 1 PROFITEST H+E TECH test instrument
- 2 9 V block batteries
- 1 12 V power pack
- 1 Set of operating instructions



# **Order Information**

Designation	Туре	Article Number
Communication tester between the charging station and the vehicle (connector socket and type 2 plug)	PROFITEST H+E TECH	M525B

Edited in Germany • Subject to change without notice • PDF version available on the Internet



GMC-I Messtechnik GmbH Südwestpark 15 90449 Nürnberg, Germany Phone: +49-911-8602-111 Fax: +49 911 8602-777 e-mail info@gossenmetrawatt.com www.gossenmetrawatt.com