

## HD 2302.0



# HD2302.0 **PHOTO-RADIOMETER**

The HD2302.0 is a portable instrument with a large LCD display. It measures illuminance, luminance, PAR and irradiance (across VIS-NIR, UVA, UVB and UVC spectral regions or measurement of irradiance effective according to the UV action curve). The probes are equipped with the SICRAM automatic detection module: in addition to detection, the unit of measurement selection is also automatic. The factory calibration data are already memorized inside the instruments. The Max, Min and Avg function calculate the maximum, minimum or average values. Other functions include: the relative measurement REL, the HOLD function, and the automatic turning off that can also be excluded. The instruments have IP67 protection degree.

#### **INSTRUMENT TECHNICAL CHARACTERISTICS**

Instrument

Dimensions

(Length x Width x Height) 140x88x38mm 160g (complete with batteries)

Weight Materials

Display 2x41/2 digits plus symbols - 52x42mm

Visible area: 52x42mm

Operating conditions

Operating temperature -5...50°C Storage temperature -25...65°C

Working relative humidity 0...90%RH without condensation

**Protection degree** 

Power

**Batteries** 3 1.5V type AA batteries

Autonomy 200 hours with 1800mAh alkaline batteries

Power absorbed with the instrument off  $20\mu A$ 

Measuring unit lux - fcd - μmol/m<sup>2</sup>·s - cd/m<sup>2</sup> - W/m<sup>2</sup> - μW/cm<sup>2</sup>

μW/lumen

Connections


Input module for the probes 8-pole male DIN45326 connector Technical characteristics of photometric and radiometric probes equipped with SICRAM module for the connection the instrument.

LP 471 PHOT probe for the measure of ILLUMINANCE							
Measuring range (lux):	0.10199.991999.919999199.99-10						
Resolution (lux):	0.01 0.1 1 0.01·10³						
Spectral range:	in agreem	ent with sta	ndard photopic	curve V(λ)			
$\alpha$ (temp. coefficient) $f_6$ (T)		<0	.05%K				
Calibration uncertainty:		•	<4%				
$f'_1$ (in agreement with photopic response $V(\lambda)$ ):	<6%						
f <sub>2</sub> (response according to the cosine law):	<3%						
f <sub>3</sub> (linearity):		<	<1%				
f <sub>4</sub> (instrument reading error):		<	0.5%				
f <sub>5</sub> (fatigue):		<	0.5%				
Class	В						
Drift after 1 year:	<1%						
Working temperature:	050°C						
Reference Standards	CIE n.69 - UNI 11142						

Photometric probe for **ILLUMINANCE** measurement, spectral response in agreement with standard photopic vision, diffuser for cosine correction. Measurement range: 0.10 lux...200·103 lux.



LP 471 LUM 2 probe for the measure of LUMINANCE						
Measuring range (cd/m²):	1.01999.919999199.99·10 <sup>3</sup> 1999.9					
Resolution (cd/m²):	0.1 1 0.01·10 <sup>3</sup> 0.1·10 <sup>3</sup>					
Optical angle:			2°			
Spectral range:	in agree	ment with st	andard photopic	curve V(λ)		
$\alpha$ (temp. coefficient) $f_6$ (T)		<	0.05%K			
Calibration uncertainty:			<5%			
$f'_1$ (in agreement with photopic response $V(\lambda)$ ):	<8%					
f <sub>3</sub> (linearity):			<1%			
f <sub>4</sub> (instrument reading error):		<	<0.5%			
f <sub>5</sub> (fatigue):		•	<0.5%			
Class	С					
Drift after 1 year:	<1%					
Working temperature:	050°C					
Reference Standards		CIE n.69 - UNI 11142				




LP 471 PAR quantum radiometric probe for the measure of the photon flow across the chlorophyll range PAR						
Measuring range (µmol·m <sup>-2</sup> s <sup>-1</sup> ):	0.10199.99   200.01999.9   20001000					
Resolution (µmol·m <sup>-2</sup> s <sup>-1</sup> ):	0.01 0.1 1					
Spectral range:	400nm700nm					
Calibration uncertainty:	<5%					
$f_2$ (response according to the cosine law):	<6%					
f <sub>3</sub> (linearity):	<1%					
f <sub>4</sub> (instrument reading error):		±1digit				
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<1%					
Working temperature:	050°C					

Quantum radiometric probe for the measurement of the photon flow across the chlorophyll range **PAR** (Photosynthetically Active Radiation 400nm...700nm), measurement in  $\mu$ mol/m²s. Measurement range: 0.10  $\mu$ mol·m²s¹...10·10³  $\mu$ mol·m²s⁵¹...10·10³  $\mu$ mol·m²s⁵¹.




Typical response	curve: LP	471 PAR
------------------	-----------	---------



LP 471 UVA probe for the measure of UVA IRRADIANCE							
Measuring range (W/m²):	1.0·10 <sup>-3</sup> 999.9·10 <sup>-3</sup>	1.000 19.999	20.00 199.99	200.0 1999.9			
Resolution (W/m²):	0.1·10-3	0.1·10 <sup>-3</sup> 0.001 0.01 0.1					
Spectral range:	3	315nm400nm (Peak 360nm)					
Calibration uncertainty:	<5%						
f <sub>3</sub> (linearity):	<1%						
f <sub>4</sub> (instrument reading error):	±1digit						
f <sub>5</sub> (fatigue):	<0.5%						
Drift after 1 year:	<2%						
Working temperature:		0	50°C				

Radiometric probe for **IRRADIANCE** measurement, in the 315nm...400nm, peak 360nm, UVA spectral range. Measurement range: 1.0·10<sup>-3</sup>W/m²...2000W/m².

Typical response curve: LP 471 UVA



LP 471 RAD probe for the measure of IRRADIANCE						
Measuring range (W/m²):	1.0·10 <sup>-3</sup> 1.000 20.00 200. 999.9·10 <sup>-3</sup> 19.999199.					
Resolution (W/m²):	0.1·10-3	0.001	0.01	0.1		
Spectral range:		400nm1	1050nm			
Calibration uncertainty:	<5%					
f <sub>2</sub> (response according to the cosine law):	<6%					
f <sub>3</sub> (linearity):	<1%					
f <sub>4</sub> (instrument reading error):	±1digit					
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<1%					
Working temperature:		050	)°C			

Radiometric probe for **IRRADIANCE** measurement in the spectral range 400nm...1050nm, diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>W/m<sup>2</sup>...2000W/m<sup>2</sup>.

Typical response curve: LP 471 RAD





LP 471 UVB probe for the measure of UVB IRRADIANCE						
Measuring range (W/m²):	1.0·10·3  1.000  20.00  200.0   999.9·10·3 19.999 199.99 1999.9					
Resolution (W/m²):	0.1·10 <sup>-3</sup> 0.001 0.01 0.1					
Spectral range:	280n	ım315nm (P	eak 305nm31	Onm)		
Calibration uncertainty:	<5%					
f <sub>3</sub> (linearity):	<2%					
f <sub>4</sub> (instrument reading error):	±1digit					
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<2%					
Working temperature:	050°C					

 $\lambda$  (nm)

Radiometric probe for **IRRADIANCE** measurement, in the spectral range 280nm...315nm, peak 305nm ... 310nm, Measurement range: 1.0·10<sup>-3</sup>W/m²...2000W/m².

Typical response curve: LP 471 UVB






LP 471 UVC probe for the measure of UVC IRRADIANCE						
Measuring range (W/m²):	1.0·10·3  1.000  20.00  200.   999.9·10·3 19.999 199.99 199					
Resolution (W/m²):	0.1·10 <sup>-3</sup>	0.001	0.01	0.1		
Spectral range:	220nm280nm (Peak 260nm)					
Calibration uncertainty:	<5%					
f <sub>3</sub> (linearity):	<1%					
f <sub>4</sub> (instrument reading error):	±1digit					
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<2%					
Working temperature:	050°C					

Radiometric probe for **IRRADIANCE** measurement, in the spectral range 220nm...280nm, peak 260nm, UVC. Measurement range:  $1.0 \cdot 10^{-3}$ W/m²...2000W/m².

Typical response curve: LP 471 UVC





Combined probe LP 471 P-A with two sensors for the measure of ILLUMINANCE and UVA IRRADIANCE					
Illuminance					
Measuring range (lux):	0.10199.9	1999.9	19999	199.99-103	
Resolution (lux):	0.01	0.1	1	0.01·10 <sup>3</sup>	
Spectral range:	in agreemen	t with stand	dard photo	pic curve V(λ)	
$\alpha$ (temp. coefficient) $f_6$ (T)		<0.0	)5%K		
Calibration uncertainty:		<4	1%		
$f'_1$ (in agreement with photopic response $V(\lambda)$ ):	<6%				
f <sub>2</sub> (response according to the cosine law):		<:	3%		
f <sub>3</sub> (linearity):		<	1%		
f <sub>4</sub> (instrument reading error):		<0	.5%		
f <sub>5</sub> (fatigue):		<0	.5%		
Class:	В				
Drift after 1 year:	<1%				
Working temperature:	050°C				
Reference Standards	CIE n.69 - UNI 11142				


Please refer to the spectral response of the LP471PHOT probe

UVA Irradiance						
Measuring range (µW/cm²):	0.10199.991999.919999199.99-10					
Resolution (µW/cm²):	0.01	0.1	1	0.01·10 <sup>3</sup>		
Spectral range:	315n	m400nm	(Peak 360	nm)		
Calibration uncertainty:	<5%					
f <sub>2</sub> (response according to the cosine law):		<6'	%			
f <sub>3</sub> (linearity):		<1'	%			
f <sub>4</sub> (instrument reading error):		±1d	igit			
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<2%					
Working temperature:		05	0°C			

Please refer to the spectral response of the LP471UVA probe




LP 471 A-UVeff probe for the measure of TOTAL EFFECTIVE IRRADIANCE weighted according to the UV action curve (CEI EN 60335-2-27)					
Total Effective Irradiance					
Measuring range (W <sub>eff</sub> /m <sup>2</sup> ):	0.010 19.999				
Resolution (W <sub>eff</sub> /m <sup>2</sup> ):	0.001				
Spectral range:	UV action curve for measuring erythema (250 nm400 nm)				
Calibration uncertainty:	<15%				
f <sub>3</sub> (linearity):	<3%				
f <sub>4</sub> (instrument reading error):	±1 digit				
f <sub>5</sub> (fatigue):	<0.5%				
Drift after 1 year:	<2%				
Working temperature:	050°C				
Reference standard	CEI EN 60335-2-27				
UVA Irradiance					
Measuring range (W <sub>eff</sub> /m <sup>2</sup> ):	0.01 1999.9				
Resolution (W <sub>eff</sub> /m <sup>2</sup> ):	0.1				
Spectral range:	315 nm 400 nm				
UV_BC Irradiance					
Measuring range (W <sub>eff</sub> /m <sup>2</sup> ):	0.010 19.999				
Resolution (W <sub>eff</sub> /m <sup>2</sup> ):	0.001				
Spectral range:	250 nm 315 nm				






LP SILICON-PYRA probe for the measure of GLOBAL SOLAR RADIATION						
Measurement range (W/m²):	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$					
Resolution (W/m²):	0.1.10-3	0.001	.01	0.01		
Spectral range:		400 nm	1 1100 nm			
Calibration uncertainty:	<3%					
f <sub>2</sub> (response according to the cosine law):	<3%					
f <sub>3</sub> (linearity):	<1%					
f <sub>4</sub> (instrument reading error):		:	±1 digit			
f <sub>5</sub> (fatigue):	<0.5%					
Drift after 1 year:	<2%					
Working temperature:	050°C					



LP 471 BLUE probe for the measure of IRRADIANCE in spectral band of BLUE LIGHT				
Measurement range (W/m²):	1.0·10 <sup>-3</sup> 999.9·10 <sup>-3</sup>	1.00019.999	20.00199.99	200.01999.9
Resolution (W/m²):	0.1·10-3	0.001	.01	0.01
Spectral range:	380 nm 550 nm. Action curve for damages of Blue light $B(\lambda)$			
Calibration uncertainty:	<10%			
f <sub>2</sub> (response according to the cosine law):	<6%			
f <sub>3</sub> (linearity):	<3%			
f <sub>4</sub> (instrument reading error):	±1 digit			
f <sub>5</sub> (fatigue):	<0.5%			
Drift after 1 year:	<2%			
Working temperature:	050°C			



The radiometric probe LP 471-BLUE measures irradiance (W/m<sup>2</sup>) in spectral band of blue light. The probe consists of a photodiode plus an appropriate filter and it is provided with diffuser for proper measure in accordance with the cosine law. The spectral response curve of the probe allows to measure the radiation effective for damages caused by blue light (curve  $B(\lambda)$ according to the standards ACGIH / ICNIRP) in the spectral range from 380nm to 550nm. The radiation optics in this portion of the spectrum can produce photochemical damage to the retina. Another field of application is the monitoring of the probe irradiance from blue light used in the treatment of neonatal jaundice.

#### **ORDERING CODES**

HD2302.0: The kit consists of the instrument HD2302.0, 3 1.5V alkaline batteries, operating manual, case. The probes must be ordered separately.

### Probes complete with SICRAM module (see page LG-7)

- LP 471 PHOT: Photometric probe for measuring ILLUMINANCE complete with SICRAM module, spectral response in agreement with standard photopic vision, Class B according to CIE n°69, diffuser for cosine correction. Measurement range: 0.10 lux...200·103 lux.
- LP 471 LUM 2: Photometric probe for measuring LUMINANCE complete with SICRAM module, spectral response in agreement with standard photopic vision, vision angle 2°. Measurement range: 1.0 cd/m<sup>2</sup>...2000·10<sup>3</sup> cd/m<sup>2</sup>.
- LP 471 PAR: Quantum radiometric probe for the measurement of the photon flow across the chlorophyll range PAR (Photosynthetically Active Radiation 400nm...700nm) complete with SICRAM, measurement in µmol·m<sup>-2</sup>s<sup>-1</sup>, diffuser for cosine correction. Measurement range:  $0.10 \mu mol \cdot m^{-2}s^{-1}...10 \cdot 10^{3} \mu mol \cdot m^{-2}s^{-1}$
- LP 471 RAD: Radiometric probe for measuring IRRADIANCE equipped with SICRAM module; in the 400nm...1050nm spectral range, diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>W/m<sup>2</sup>...2000W/m<sup>2</sup>.
- LP 471 UVA: Radiometric probe for measuring IRRADIANCE equipped with SICRAM module; in the 315nm...400nm, peak 360nm, UVA spectral range, quartz diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>W/m<sup>2</sup>...2000 W/m<sup>2</sup>
- LP 471 UVB: Radiometric probe for measuring IRRADIANCE equipped with SICRAM module, in the 280nm...315nm, peak 305nm ... 310nm, UVB spectral range, quartz diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>W/m<sup>2</sup>...2000 W/m<sup>2</sup>.
- LP 471 UVC: Radiometric probe for measuring IRRADIANCE equipped with SICRAM module, in the 220nm...280nm, peak 260nm, UVC spectral range, quartz diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>W/m<sup>2</sup>...2000 W/m<sup>2</sup>
- LP 471 BLUE: Radiometric probe for measuring IRRADIANCE (W/m²) in spectral band of blue light equipped with SICRAM module. Spectral range: 380 nm...550 nm, quartz diffuser for cosine correction. Measurement range: 1.0·10<sup>-3</sup>Weff /m<sup>2</sup> ... 2000 Weff /m<sup>2</sup>.
- LP 471 P-A: Combined probe for measuring ILLUMINANCE (lux), with standard photopic response, and IRRADIANCE (µW/cm2) in the UVA spectral range (315...400 nm, with peak at 360 nm). Both the sensors are equipped with diffuser for the correction according to the cosine law.

Illuminance measuring range: 0.10 lux ... 200·103 lux

Irradiance measuring range: 1.0 mW/m<sup>2</sup> ... 2000 W/m<sup>2</sup>.

This probe provides the ratio between UVA irradiance and illuminance in µW/lumen (quantity of interest in museums). The probe is equipped with SICRAM module and cable 2m long.

LP 471 A-UVeff: Combined probe for measuring the TOTAL EFFECTIVE IRRADIANCE (W/m²) weighted according to the UV action curve. The probe is made of two sensors for the correct measure of the Total Effective Irradiance in the range 250...400nm. Both these sensors are equipped with a diffuser for the correction according to the cosine law. This probe supplies the Total effective irradiance (Eeff), the UV-CB effective irradiance

and the UVA Irradiance. Total effective irradiance measuring range: 0.010 W/m<sup>2</sup> ... 20 W/m<sup>2</sup>. B\_C effective irradiance measuring range: 0.010 W/m<sup>2</sup> ... 20 W/m<sup>2</sup>.

UVA irradiance measuring range: 0.1 W/m<sup>2</sup> ... 2000 W/m<sup>2</sup>

The probe is equipped with the SICRAM module and a cable 2m long.

LP 471 PYRA 02..., LP PYRA 03..., LP PYRA 10..., LP 471 Silicon-PYRA...

- See page LG-7
- LP BL: Base with levelling device for all the above-described probes except for the probes LP 471 LUM 2 and LP 471 PYRA.
- LP BL3: Jointed support for all the above-described probes except for LP 471 LUM 2 and LP 471 PYRA.

