



Datasheet

Item no. 1588988, 1589080, 1589081, 1589082, 1589214, 1589212, 1589083, 1589084, 1589213, 1589357, 1589027, 1589358, 1589359, 1589360, 1589150, 1589028, 1589361, 1589151, 1589362, 1589363, 1589364, 1589029, 1589365, 1589152, 1589366, 1589153, 15893678, 1589154



Part No	Inductance L (nH)	f_L (MHz)	Tol \pm (%)	Q min	f_Q (MHz)	SRF (MHz)	DCR max (Ω)	Rated DC Current (mA)
TC-0603AS-010J203	10	250	5	31	250	4800 min	0.13	700
TC-0603AS-015J203	15	250	5	35	350	4000 min	0.17	700
TC-0603AS-022J203	22	250	5	38	250	3000 min	0.19	700
TC-0603AS-R10J203	100	150	5	34	150	1400 min	0.58	400
TC-0603AS-R22J203	220	100	5	30	100	1000 min	1.60	150
TC-0603AS-2N2M203	2.2	250	20	10	250	5900 min	0.17	170
TC-0603AS-R33J203	330	100	5	25	100	600 min	2.50	150
TC-0603AS-R47J203	470	25	10	16	25	230 typ	2.80	150
TC-0603AS-4N7J203	4.7	250	10	25	250	> 6000 min	0.07	700
TC-0603AS-010J-01203	10	250	5	31	250	4800 min	0.13	700
TC-0603AS-015J-01203	15	250	5	35	250	4000 min	0.17	700
TC-0603AS-022J-01203	22	250	5	38	250	2800 min	0.19	700
TC-0603AS-033J-01203	33	250	5	40	250	2300 min	0.22	600
TC-0603AS-047J-01203	47	200	5	38	200	2000 min	0.28	600
TC-0603AS-R68J-01203	680	25	10	16	25	140 typ	3.00	140
TC-0603AS-068J-01203	68	200	5	37	200	1700 min	0.34	400
TC-0603AS-2N2J-01203	2.2	250	20	10	250	5900 min	0.17	170
TC-0603AS-3N3J-01203	3.3	250	10	22	250	6000 min	0.10	700
TC-0603AS-4N7J-01203	4.7	250	10	25	250	> 6000 min	0.07	700
TC-0603AS-R15J-01203	150	150	5	32	150	1200 min	0.90	200
TC-0603AS-R10J-01203	100	150	5	34	150	1400 min	0.58	400
TC-0603AS-R22J-01203	220	100	5	30	100	1000 min	1.60	150
TC-0603AS-R47J-01203	470	25	10	16	25	230 typ	2.80	150
TC-0603AS-R33J-01203	330	100	5	25	100	600 min	2.50	150
TC-0603AS-R33J-08203	330	100	5	25	100	600 min	2.50	150
TC-0603AS-R47K-08203	470	25	10	16	25	230 typ	2.80	150
TC-0603AS-1N5K-08203	1.5	250	10	20	250	> 6000 min	0.030	850
TC-0603AS-R22J-08203	220	100	5	30	100	1000 min	1.60	150

