





Datasheet

Item no. 1589187, 1589061, 1589190, 1589185, 1589186, 1589188, 1589060, 1589189, 1589191



Part No	Inductance L (nH)	f_L (MHz)	Tol \pm (%)	Q (min)	f_Q (MHz)	SRF (MHz)	DCR max (Ω)	Rated DC Current max (mA)
TC-1206AS-068K203	68	100	5	61	300	1200 min	0.26	900
TC-1206AS-2R2K203	2200	35	10	32	150	160 typ	4.50	280
TC-1206AS-R33J-01203	330	50	5	55	150	650 min	0.62	590
TC-1206AS-010J-01203	10	100	5	40	300	4000 min	0.08	1000
TC-1206AS-047J-01203	47	100	5	64	300	1500 min	0.13	1000
TC-1206AS-R10J-01203	100	100	5	55	300	1100 min	0.26	850
TC-1206AS-R15J-01203	150	100	5	65	300	950 min	0.31	750
TC-1206AS-R22J-01203	220	50	5	75	300	760 min	0.50	670
TC-1206AS-R47J-01203	470	50	5	52	150	550 min	1.30	490

