

Datasheet

Item no. TC-DS2X6L

ELECTRICAL & MECHANICAL SPECIFICATION

Switch Rating:	150mA @ 250V ac/dc	Life:	>10,000 Cycles
	1A @ 24V dc	Operating Temperature:	-30°C to +85°C
Proof Voltage:	1,500V ac (Initial)	Operating Torque (nominal):	Standard 8.6 ±1 cNm
Insulation Resistance:	>999 MΩ at 500V dc (Initial)	End Stop Torque (nominal):	Light Action 3.5 ± 0.5 cN
Contact Resistance	<20 mΩ (Initial)	Moulding Material:	Polyamide 6.6 G.F
Contact/Terminal Material:	Brass CZ108 Ag Plated		

FEATURES

- Single wafer switch non shorting (break before make) Solder
- 2 x 6 positions Made in UK
- Standard 30° indexing,
- Moulded 27.5mm diameter

