



Hi-Speed USB A Device Cable

USB 2.0, Type-A Male to Type-A Male, 480 Mbps, 1.8 m (6 ft.), Black

Part No.: [306089](#)

EAN-13: 0766623306089 | UPC: 766623306089

Connect with confidence.

Manhattan Hi-Speed USB Device Cables easily connect USB peripherals and accessories with desktop and notebook computers. They're ideal for use with many USB external enclosures, hubs and other hot-swap, Plug and Play devices. Manhattan Hi-Speed USB Device Cables support data transfer rates up to 480 Mbps on Windows and Mac systems for fast, reliable data transmissions. Gold-plated contacts and fully molded boots with strain relief help provide dependable connections, maximum conductivity and minimal data loss.

Features:

- USB 2.0 Type-A male to Type-A male
- Connects a USB device to a USB hub or computer
- Supports speeds of up to 480 Mbps
- Ideal replacement or spare cable for synchronization and charging
- Lifetime Warranty

Specifications:

Standards and Certifications

- UL 2725

Connectors

- Two USB 2.0 Type-A male
- Gold-plated contacts
- Molded PVC boot with strain relief

Cable

- Shielded
- Current rating: 0.5 ADC
- Withstanding voltage: 300 VDC
- Insulation resistance: 5 MOhm
- Conductive resistance: 5 Ohm

- Thermal plastic casing
- 28 AWG

Physical

- Length: 1.8 m (6 ft.)
- Weight: 48 g (1.7 oz.)

Operating Environment

- Operation temperature: 0 - 50°C (32 - 122°F)
- Storage temperature: -25 - 85°C (-13 - 185°F)
- Humidity (noncondensing): 0 - 96%

Package Contents

- Hi-Speed USB Device Cable

