

DATASHEET





Self Adhesive Tie Mount

Technical data











Item No.	Bundle Φ max. (mm)	Mounting Φ (mm)	Colour	Dimensions (W x H x L) (mm)
1593034	3	3	Transparent	18.9 x 4.6 x 18.9
1593035	6.4	4.8	Black	18.9 x 4.6 x 18.9
1593036	12.7	5	Transparent	26.3 x 5.3 x 26.3
1593037	9.5	4.3	Black	26.1 x 6 x 26.1
1593038	12.7	5	Transparent	26.3 x 5.3 x 26.3
1593039	25.4	4.3	Black	26.5 x 7.4 x 26.5
1593040	19.4	4.3	Transparent	26.5 x 7.4 x 26.5
1593041	19.4	4.3	Black	26.5 x 5.8 x 26.5
1593042	7	4.4	Transparent	19 x 5 x 19
1593043	10.1	4.4	Black	19 x 5 x 19
1593044	4.8	5	Transparent	28.6 x 5.3 x 28.6
1593045	3.6	5	Black	28.6 x 5.3 x 28.6
1593046	4.8	5	Transparent	29.2 x 5.4 x 29.2
1593047	4.4	5	Black	29.2 x 5.4 x 29.2
1593048	7	4.4	Transparent	19 x 5 x 19
1593049	10.1	4.4	Black	19 x 5 x 19
1593050	13.4	5	Transparent	38.5 x 7.6 x 38.5
1593051	16.2	5	Black	38.5 x 7.6 x 38.5




Product type Mounting base
Material Polyamide 6.6
Packing 100 pcs/polybag
Adhesive application temperture +10 to +40 °C
Operating conditions -40 to +85 °C

Overview

Item no: 1593034 	Item no: 1593035 
Item no: 1593036 	Item no: 1593037 



Item no: 1593038  With Adhesive Tape	Item no: 1593039  With Adhesive Tape
Item no: 1593040  With Adhesive Tape	Item no: 1593041  With Adhesive Tape
Item no: 1593042  With Adhesive Tape	Item no: 1593043  With Adhesive Tape
Item no: 1593044  With Adhesive Tape	Item no: 1593045  With Adhesive Tape
Item no: 1593046  With Adhesive Tape	Item no: 1593047  With Adhesive Tape

Item no: 1593048 	Item no: 1593049 
Item no: 1593050 	Item no: 1593051 