


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
5/06/06	D	ADDED CONTACT RESI. INFO	T.B.	B.S.	
10/02/09	E	REDRAWN. DIM. 59.70 WAS 56.30 DIM. 13.70 WAS 13.00 DIM. 16.00 WAS 16.40	T.B.	B.S.	
10/24/14	F	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
06/30/17	G	ADDED DIM. Ø2.54	T.B.	B.S.	
07/22/17	H	ADDED MOUNTING INSTRUCTION	T.B.	B.S.	




**NOTES:**

- Plastic material - Polypropylene, Black
- Flammability Rating -UL94-HB, UL File NO. E216959
- Temperature Range: -10°C to +100°C
- Springs - Nickel Plated Spring Steel
- Rivets - Brass, Nickel Plated
- Wires - 26 AWG, UL1007, CSA -TR-64, 300V, 80°C
- Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000
- ROHS 2 COMPLIANT

**Mounting Instruction:**

Use 2-56 machine screws or eyelets 0.089" OD by 0.15" flange stimpson GS-3 series or equivalent. also adhesives and double sided tapes work well.

Tolerance (Except as noted)	 <b>Memory Protection Devices, Inc</b> 200 Broad Hollow Road, Farmingdale, New York 11735		
	decimal ±.5 (.020)	Scale	Drawn By B.S. Approved By T.B.
Fractional ± .8 (.030)	Title ONE "AA" CELL HOLDER WITH WIRE LEADS		
Angular ± 3°	Date 07/22/17	Drawing Number BCAAW	