



PLASTICA PANARO s.r.l.

LAVORAZIONE PLASTICA STAMPATA



CAPITALE SOCIALE € 104.520,00 I.V.
Via Gramsci, 438 - 41054 MARANO s. P. (MO) Italia
Registro Imprese di Modena n. 00156160368 - R.E.A. MO n. 104468
Codice Fiscale 00156160368 - Partita IVA IT 00156160368 - Export MO / 003846
Tel. 059.793340 (3 linee ISDN R.A.) - Fax 059.705052
E-mail: info@plasticapanaro.it - <http://www.plasticapanaro.it>

MAX™

MAX750H400

OVERVIEW

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Thick body material
- Fully length hinges
- Nylon pins, corrosion free
- Cubed foams in the bottom and convoluted foams in the lid available as standard
- Screen printing space and rectangular resin label space on the lid

Body and handle: polypropylene copolymer

Latches: nylon

Pins (for locks): nylon + 30% fiberglass - Pins (for wheels): Stainless steel

O-ring: polymer

COLOURS:



EXTERNAL DIMENSIONS: 816 x 540 x H426 mm (32.12 x 21.26 x H16.77 inch)

INTERNAL DIMENSIONS: 750 x 480 x H400 mm (29.52 x 18.90 x H15.75 inch)

LID-BOTTOM DEPTH: 60 + 340 mm (2.36 + 13.38 inch)

WEIGHT W/O FOAM: 12100 g

WEIGHT WITH FOAM: 13700 g

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67 FEATURES: wheels, IP67, large fold down handle

CUSTOMIZATION: personalized nameplate/ resin label

ACCESSORIES: cubed foams

