

## VOLTcraft® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

## CNPS-45



# COMPACT USB-C POWER ADAPTER

VERSION 02/18

Nº 1601915

This product is designed to charge and power compatible USB-C™ devices. Power is supplied via a standard household mains socket. The product is protected against overloads and short circuits. It automatically recognizes the charging parameters using Power Delivery technology, enabling quick and efficient charging for a range of different devices.

This product is intended for indoor use only. Do not use it outdoors. Contact with moisture (e.g. in bathrooms) must be avoided under all circumstances.

## HIGHLIGHTS

**USB power delivery up to 20 V / 45 W //**

**Built-in circuit automatically detects the charging specifications //**

**Overload protection //**

## TECHNICAL DATA

Input voltage/current	100–240 V/AC, 50/60 Hz, max. 1 A
Output voltages/currents	5 V/DC, 9 V/DC, 12 V/DC, 15 V/DC / 3 A; 20 V/DC, 2.25 A
Power	Max. 45 W (overload protection up to max. 55 W)
Surge protection	5/9/12 V up to max. 3.9 A; 20 V up to max. 2.9 A
Ripple	220 mV p-p max.
USB type	USB-C™
Efficiency class	Level VI
Colour	Black
Operating conditions	0 to +35 °C, 10–95 % relative humidity (non-condensing)
Storage conditions	-10 to +55 °C, 5–95 % relative humidity (non-condensing)
Dimensions (W x H x D)	94 x 56 x 28 mm
Weight	116 g



## PACKAGE CONTENT

USB power adapter // USB-C™ cable // Operating instructions //

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.