
LCD time modules | Max. time range 9999.99 h (DC) | 194



The timer module of the type 194 for PCB mount features a 6-digit LCD display and 2 voltage ranges (4.75 ... 15 V DC and 9 ... 60 V DC).

It is extremely robust and suitable for many different applications thanks to its wide temperature range.



Timer | Supply voltage | Input type | High shock resistance | Temperature range | PCB mount | LCD display | Electrical reset

Powerful

- Display range up to 9999-99 hours.
- 6-digit LCD display, 6 mm high.
- Low power consumption.
- Wide voltage and temperature range.
- Very high shock and vibration resistance.

Simple

- Non-volatile memory (no battery).
- Counting starts as soon as supply voltage is applied.
- Electrical reset.
- Very high reliability.
- Small size and low cost.

Order specifications

Supply voltage	*Order no.*	*Art.-No.*
4.75 ... 15 V DC	**6.194.012.F00**	162 137
9 ... 60 V DC	**6.194.012.G00**	162 138

Delivery specification
- LCD hour meter module type 194
- Operating instructions

© Fritz Kübler GmbH, subject to errors and changes. 02/2024

LCD time modules | Max. time range 9999.99 h (DC) | 194

Technical data

General technical data

Display	6 digits, LCD display, figure height 6 mm [0.24“]
Display range	9999-99 h
Data backup	CMOS EEPROM non-volatile memory up to 10 years
Operating temperature	-40 °C ... +85 °C [-40 °F ... +185 °F] (non-condensing)
Working temperature	-20 °C ... +80 °C [-4 °F ... +176 °F] (non-condensing)
Storage temperature	-50 °C ... +90 °C [-58 °F ... +194 °F]

Electrical characteristics

Supply voltage	...F00	4.75 ... 15 V DC, with reverse polarity protection
	...G00	9 ... 60 V DC
Current consumption	...F00	8 mA at 4.75 ... 15 V DC
	...G00	6 mA at 9 ... 60 V DC

The module must be protected against inductive voltage spikes and high energy noise interference.

Mechanical characteristics

Housing	color	black
Weight		approx. 8 g [0.28 oz]
Shock resistance acc. to DIN-IEC 68-2-27		550 m/s^2, 11 ms
Vibration resistance acc. to DIN-IEC 68-2-6		50 ... 200 m/s^2, 10 ... 80 Hz

Inputs


Reset input	HIGH	4 ... 60 V DC
	LOW	0 ... 0.7 V DC
	pulse length	min. 1 ms, edge triggered (rising)
Measuring error		a max. error of 36 sec. occur per Start/Stop cycle
Accuracy (Quarz)		max. 200 ppm 25 °C [+77 °F]

Approvals

CE compliant in accordance with


EMC Directive	2014/30/EU
RoHS Directive	2011/65/EU


Terminal assignment



Dimensions

Dimensions in mm [inch]





© Fritz Kübler GmbH, subject to errors and changes. 02/2024