


# NodeMCU ESP8266

Microcontroller Development Board



## Technical Specifications

<b>Model</b>	NodeMCU ESP8266
<b>Article No.</b>	SBC-NodeMCU
<b>Type</b>	ESP8266
<b>Processor</b>	Tensilica LX106
<b>Clock Frequency</b>	80 - 160 MHz
<b>RAM</b>	64 kB
<b>Data Storage</b>	96 kB
<b>Wireless Standard</b>	802.11 b/g/n
<b>Frequency</b>	2.4 GHz
<b>Data Interfaces</b>	UART / I2C / PWM / GPIO
<b>Operating Voltage</b>	3.0 - 3.6 V (operable via 5V-microUSB)
<b>Operating Current</b>	80mA
<b>Operating Temperature</b>	-40°C - 125°C
<b>Dimensions (W x D x H)</b>	58 x 31 x 12 mm
<b>Scope Of Delivery</b>	NodeMCU ESP8266
<b>EAN</b>	4250236815923